

GPS460

Magnetic Mount GPS Antenna

Features

- ◆ Active GPS Antenna
- ◆ Magnetic Mount
- ◆ Discrete Design
- ◆ Ideal for fleet applications

Specifications

Frequency	1575.42
Polarisation	RHCP
LNA gain	26 dB
Noise Figure	2.0 dB max
Voltage	3V/5V
Power Consumption	20 mA (max)
Cable / Connector	3M RG-174 and SMA-Male
Dimensions	45x45x14.6mm

Ordering Options

FGPX35136-SM-3K	GPS460 with 3M RG-174 and SMA-Male
-----------------	------------------------------------

www.ead-ltd.com

Specifications subject to change without notice.

Unit 19, Hillcrest Way
Buckingham Industrial Park
Buckingham
MK18 1HJ
UK

Tel: +44 (0)1280 825537
Fax: +44 (0)1280 817179
Email: sales@ead-ltd.com
Web: www.ead-ltd.com


EAD
embedded antenna design ltd



GPS460 | Magnetic Mount GPS Antenna

Return Loss

Outline Drawing



Specifications subject to change without notice.

5 Little Balmer
Buckingham Industrial Park
Buckingham
MK18 1TF
UK

Tel: +44 (0)1280 825537
Fax: +44 (0)1280 817179
Email: sales@ead-ltd.com
Web: www.ead-ltd.com