

O-Ring

Metr., PG, NPT



O-Ring Buna-N

Material Buna-N

Operating Temperature -30 °C – 120 °C (-22 °F – 248 °F)

O-Ring FPM

Material FPM

Operating Temperature -40 °C – 200 °C (-40 °F – 392 °F)

O-Ring VMQ


Material VMQ (Silicone)

Operating Temperature -60 °C – 250 °C (-76 °F – 482 °F)

RoHS



O-Ring for HSK-K



Fits the following sizes	d mm	s mm	Number Buna-N	Number FPM	Number VMQ
M 12 x 1,5	10	1,5	1.321.1200.57	1.321.1200.58	1.321.1200.59
M 16 x 1,5	12	1,5	1.321.1600.57	1.321.1600.58	1.321.1600.59
M 20 x 1,5	17	1,8	1.321.2000.57	1.321.2000.58	1.321.2000.59
M 25 x 1,5	22	2	1.321.2500.57	1.321.2500.58	1.321.2500.59
M 32 x 1,5	29	2	1.321.3200.57	1.321.3200.58	1.321.3200.59
M 40 x 1,5	35	2	1.321.4000.57	1.321.4000.58	1.321.4000.59
M 50 x 1,5	43	2	1.321.5000.57	1.321.5000.58	1.321.5000.59
M 63 x 1,5	55	2	1.321.6300.57	1.321.6300.58	1.321.6300.59
PG 7	10	1,5	1.321.0700.17	1.321.0700.21	1.321.0700.22
PG 9	12	1,5	1.321.0900.17	1.321.0900.21	1.321.0900.22
PG 11	16	1,5	1.321.1100.17	1.321.1100.21	1.321.1100.22
PG 13,5	17	1,8	1.321.1300.17	1.321.1300.21	1.321.1300.22
PG 16	18	1,5	1.321.1600.17	1.321.1600.21	1.321.1600.22
PG 21	26	2	1.321.2100.17	1.321.2100.21	1.321.2100.22
PG 29	33	2	1.321.2900.17	1.321.2900.21	1.321.2900.22
PG 36	43	2	1.321.3600.17	1.321.3600.21	1.321.3600.22
PG 42	50	2	1.321.4200.17	1.321.4200.21	1.321.4200.22
PG 48	55	2	1.321.4800.17	1.321.4800.21	1.321.4800.22
3/8" NPT	13	2	1.321.3800.77	1.321.3800.78	1.321.3800.79
1/2" NPT	19	1,8	1.321.1200.77	1.321.1200.78	1.321.1200.79
3/4" NPT	22	2	1.321.3400.77	1.321.3400.78	1.321.3400.79
1" NPT	29	2	1.321.1000.77	1.321.1000.78	1.321.1000.79
1 1/4" NPT	38	2,5	1.321.5400.77	1.321.5400.78	1.321.5400.79
1 1/2" NPT	45	2,5	1.321.6400.77	1.321.6400.78	1.321.6400.79