

Multipurpose Enclosures

Sealed ABS and Polycarbonate



Features:

- Material : Polycarbonate
- Moulded in : Light grey.
- Operating temperature : -40°C to 120°C
- Clear lid is available on request
- High impact ABS material
- Mould in : Dark gray.
- Suggested operating temperature : -20°C to 80°C
- The lid and base incorporate a tongue and groove sealing system with a neoprene gasket.
- Wall mounting holes and lid fixing screws are outside the sealing area thus preventing the ingress of moisture and dust.
- Designed to IP 65 of IEC 529 and nema 4 (dust and hoseproof).
- Available with clear or light gray LIDS.
- Internal guide slots for mounting PCB assemblies vertically.
- Bosses on internal base allow fixing of PCB's horizontally or connection of terminals, etc into threaded brass inserts.
- Lid fixing screw are M-4 stainless steel (non-magnetic) into threaded brass inserts.

Specification Table

Description	Colour	Material	Part Number
BOX, ABS, IP65, GREY	Dark Grey	ABS	G302
BOX, ABS, IP65, GREY			G304
BOX, ABS, IP65, GREY			G308
BOX, ABS, IP65, GREY			G311
BOX, ABS, IP65, GREY			G313
BOX, ABS, IP65, GREY			G317

Multipurpose Enclosures

Sealed ABS and Polycarbonate



Specification Table

Description	Colour	Material	Part Number
BOX, ABS, IP65, GREY	Dark Grey	ABS	G331
BOX, ABS, IP65, GREY			G340
BOX, ABS, IP65, GREY			G346
BOX, ABS, IP65, GREY			G353
BOX, ABS, IP65, GREY			G362
BOX, ABS, IP65, GREY			G366
BOX, ABS, IP65, GREY			G368
BOX, ABS, IP65, GREY			G373
BOX, ABS, IP65, 265X185X95MM			G378
BOX, ABS, IP65, GREY			G386
BOX, ABS, IP65, GREY			G387
BOX, ABS, IP65, GREY			G396
BOX, ABS, IP65, GREY			G399
BOX, ABS, IP65, 240X160X90MM			G3008
BOX, ABS, IP65, 240X160X120MM			G3019
BOX, ABS, IP65, 300X230X86MM			G3028
BOX, ABS, IP65, 300X230X111MM			G3031
BOX, ABS, IP65, 360X200X150MM			G3039