

REVISION M

UNLESS OTHERWISE NOTED

TOLERANCES ARE:

DIMENSIONS ARE IN INCHES
 ONE PLACE DECIMALS $\pm .1[2.5]$ THREE PLACE DECIMALS $\pm .005[.127]$ ANGLES $\pm 2^\circ$
 TWO PLACE DECIMALS $\pm .01[.25]$ FOUR PLACE DECIMALS $\pm .0020[.051]$

TITLE:
 2MM SOCKET
 STRIP ASSEMBLY

DWG NO:
 YTQ-1XX-XX-XX-X-XXX-XXX

SHEET 1 OF 2

NOTES:

1. MINIMUM CONTACT RETENTION: .5 lb PER PIN.
2. CUT FLASH TO BE .020 [.50] MAX.
3. TOE TO BE 2' MAX.
4. HEIGHT VARIANCE, PIN TO PIN: .005 [.13] MAX.
5. $\textcircled{C}$ REPRESENTS A CRITICAL DIMENSION.






FIG. 1



SECT. "A-A"



* = NOT ENGINEERING APPROVED

**** - MW OPTION, DO NOT DESIGN IN. SAMTEC WILL ONLY SUPPORT EXISTING BUSINESS 2/11/02.**




FIG. 2
 POLARIZATION OPTION LOCATION
 INSERT PK-07-N INTO SPECIFIED
 POSITION AND BREAK OFF TAB

TABLE 1		
LEAD STYLE	'A'	CONTACT
-01	.090 [2.29]	C-79-01-X
-02	.600 [15.24]	C-79-02-X
-03	.208 [5.28]	C-79-53-X

PROPRIETARY NOTE
 THIS DOCUMENT CONTAINS INFORMATION
 CONFIDENTIAL AND PROPRIETARY TO
 SAMTEC INC. AND SHALL NOT BE
 REPRODUCED OR TRANSMITTED IN
 ANY FORM OR BY ANY MEANS
 WITHOUT THE WRITTEN CONSENT OF SAMTEC INC.

CONTACT:
PHOS BRONZEMATERIAL:
BLACK, LCP

samtec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
 PHONE (812) 944-6733 P.O. BOX 1147
 CODE 55322

MADE BY:
 BRATCHER 1-26-99

YTQ-1XX-XX-XX-X-XXX-XXX
 SHEET 1 OF 2