


THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA, USA.


THIS DRAWING IS A CONTROLLED DOCUMENT.

DWG NO
621612

USED ON




POSN #1



INFOPORT SERIES III
15 POSN, KEY 2

CABLE



1	BLACK #30 AWG	P
2	WHITE #30 AWG	
3	RED #30 AWG	P
4	GREEN #30 AWG	
5	BROWN #30 AWG	P
6	BLUE #30 AWG	
7	ORANGE #30 AWG	P
8	YELLOW #30 AWG	
9	VIOLET #30 AWG	P
10	GRAY #30 AWG	
11	TAN #30 AWG	P
12	PINK #30 AWG	
13	WHITE/BLUE #30 AWG	P
14	BLUE/WHITE #30 AWG	
15	GREEN/YELLOW #30 AWG	
SHIELD	DRAIN	
SHIELD	DRAIN	

- 1 CABLE; 7.5 PAIR,30 AWG (7/38) TIN PLATED COPPER WITH PVC INSULATION.
2 DRAIN WIRES AN A ALUMINUM/POLYESTER SHIELD.
2. ASSEMBLY INSPECTED FOR OPENS AND SHORTS.
3. CABLE ASSEMBLY ALL BLACK IN COLOR, WITH NO PRINT ON JACKET.
4. MATERIALS ARE UL RECOGNIZED.

OBSOLETE

12.00±.50	621612-3
72.00±1.00	621612-2
12.00±.50	621612-1
L	PART NO

LOC
CF
DIST
39

WIRING DIAGRAM

						APPL FEED	TRIMMING BURR
						—	—
						WDW	IDW
						—	—
H		PER ECR-08-002168	30JAN08	JAK	CR	REELING	107--
P	LTR	REVISION RECORD	DATE	DWN	APVD	SPLICE	115--

WIRE RANGE	DIMENSIONS: INCHES DIMENSIONS APPLY BEFORE PLATING TOLERANCES UNLESS OTHERWISE SPECIFIED:	Tyco Electronics Corporation Harrisburg, PA 17105-3608			
INSUL RANGE	2 PLC ± - 3 PLC ± - ANGLES ± -	NAME CABLE ASSY,PIGTAIL, INFOPORT SERIES III, 15 POSN, KEY 2			
SURF AREA	CHK 10-6-95 J.HAMMER	SCALE	SIZE	DRAWING NO	REV
DWN 10-6-95 T.SMITH	APVD -	2:1	A2	621612	H
				SHEET 1 OF 1	