


[Printer Friendl](#)

[HOME](#) | [SOLUTIONS](#) | [RESOURCE!](#) | [PRODUCTS](#) | [SERVICES](#) | [LEARNING](#) SEARCH



Current refinements (click to remove) [Search Tips](#)

☐ Region USA ☐ Product FamilyAdhesive Lined Grommet Edging Polyethylene Solid Wall Text Search: 'GES99FA-C'
Your search criteria matched only one product, shown below.



Protects and insulates wires and cables from chafing against straight edges

- General purpose material for indoor use up to 122°F (50°C)
- Provided in .030" (0.8mm) thick material making it highly flexible
- Use on straight edges
- Adhesive ensures product stays in place

‡Reel packaging may contain splices.
* Order the number of reels required.

Related Products

- [Slotted Wall](#)
- [Flame Retardant Grommet Edging R...](#)
- [Grommet Edging Nylon – Slotte...](#)
- [Grommet Edging Polyethylene –...](#)
- [Grommet Edging](#)
- [...](#)

Part Number:	GES99FA-C
RoHS Compliancy Status	Compliant
Part Description:	Solid Wall Polyethylene Grommet Edging with adhesive product will stay where it is installed on straight edges.
Product Type:	Grommet Edging
Material:	Polyethylene
Color:	Natural
Height (In.):	.19
Height (mm):	4.8
Length (ft.):	100
Length (m):	30.5
Width (In.):	.17
Width (mm):	4.3
Flammability Rating:	UL HB
Ft. Per Pkg.:	100
Outside Depth (In.):	.186
Outside Depth (mm):	4.7
Outside Width (In.):	.169
Outside Width (mm):	4.3
Panel Thickness Range (	.062– .099
Panel Thickness Range (	1.6– 2.5
Temperature Range:	-40°F to 122°F(-40°C to 50°C)
Min. Order UOM:	RL
Min. Order Qty.:	1
BOM Qty. (# of Pkgs.)	0
Add to My Catalog	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.

[ViewContent Details](#)

[Evaluate](#) [Design a Solution](#) [Install & Maintain](#)

Product Bulletins:

☐ [Adhesive Lined Grommet Edging Sa101n...](#)