

Search within category

GO

BUY NOW

DESIGN / INSTALL



VB1D2B4CM48M1

The 32A, 230V vertical power strip in black has 48 IEC C-13 receptacles. It features four 16A single-pole magnetic breaker on-off switches with integral switch guard, a red LED current monitor, and dual 10' (3m) power cords with IEC 60309 - 2P+ E pin in-sleeve connectors. It complies with IEC 60950-1, EN 55022, and EN 55024 and is CE Marked. It measures 66.3H x 3.4W x 2.0D (1683mm x 89mm x 51mm). It is sold individually.

Specs	Packaging Details	Documents	★ Add to Favorites	🛒 Add to BOM
CE Compliant	Yes			
Rack PDU Type	Basic Rack PDU with Local Meter			
Monitoring	Local Meter			
Remote Outlet Switching	No			
Mount Orientation	Vertical			
Current Rating (Amps)	32A			
Input Voltage	230V - Single Phase			
Plug Type	(2) IEC 60309 - 6H 2P+E Blue Splashproof			
Output Voltage	230V			
Receptacle Type	IEC C-13			
Total Number of Outlets	48			
Depth (In.)	2.00			
Depth (mm)	50.8			
Height (In.)	66.25			
Height (mm)	1682.8			
Width (In.)	3.50			
Width (mm)	88.9			
Tool-Less Button Spacing (In.)	64.75			
Tool-Less Button Spacing (mm)	1644.7			
No. of Rack Spaces	0			
Surge Suppression	No			
Amps	32A			
Cable Length	3			
Length (In.)	71.50			
UL Recognized	No			
Voltage	230V			
RoHS Compliancy Status	Compliant			
Min. Order Qty.	1			