

SGNMA3T SERIES

MINIATURE MID-RANGE NON-MAGNETIC TRIMMER CAPACITORS

Product Highlights

- High Voltage PTFE Dielectric
- High Precision
- Multi-Turn Economical Solution



Applications

- MRI and NMR Coils
- Transmitting and Receiving Sections of MRI and NMR Machines
- Cryogenic Projects

Model Number	Capacitance Range (pF)		Q Min (at 25 MHz C Max)	Rated DC Working Voltage (V)	Dielectric Withstanding Voltage (V)
	Min	Max			
SGNMA3T1000	1.00	10.00	2,000	1,000	2,000
SGNMA3T2000	1.00	20.00	2,000	1,000	2,000

Options:

1. Wide Variety of lead configurations
2. Horizontal and vertical mounting options