








Dimensions: mm (in.)



P.C.B. Layout

**Electrical Specifications:**

- Rating: 50mA/12VDC
- Dielectric Strength: 100 V AC(50Hz or 60Hz) for 1 minute
- Contact Resistance: 100mΩ Max.
- Insulation Resistance: 100VDC 100MΩ Min.
- Life: 100,000 cycles Min.

Note:

- RoHS Compliant

Mechanical Specifications:

- Operating Temperature: -20° C to +70° C
- Storage Temperature: -30° C to +80° C
- Operating Force: 160 ± 50gf
- Stroke: .13 ± .10mm

Mouser Stock No.	Dimension (Height)
101-IG23K-EV	1.90 (.075)
101-IG33K-EV	2.50 (.098)

Tactile Switches
101-IG23K-EV, 101-IG33K-EV

Mountain Switch