



SMB Connectors, 75 Ohm

Straight and Right-Angle Plugs

Straight Plug



Right-Angle Plug



Connector Cable Range Selection Code [†]	RG/U Cable	Center Contact Plating	Outer Body Plating	Outer Contact Plating	Dielectric	Style	Straight Plug Part No.	Right-Angle Plug Part No.
B1	179, 179A, 179B 161, 187, 187A Belden 9221	Gold	Gold	Nickel	TEFLON	Commercial	414618-1	414048-6
		Gold	Gold	Gold	TEFLON	Mil Type	414947-1	
		Gold	Nickel	Nickel	TEFLON	Commercial	414618-2	1-414048-3
		Gold	Nickel	Nickel	TEFLON	Mil Type	414947-2	



Tooling—Page 134

[†]Refer to pages 14 and 15 for cable code specifications.

SMB
Connectors

Jacks

Jack



Maximum Panel Thickness .093 (2.36)

Recommended Panel Cutout

Connector Cable Range Selection Code [†]	RG/U Cable	Center Contact Plating	Body Plating	Dielectric	Style	Jack Part No.	Bulkhead Jack Part No.
B1	179, 179A, 179B 161, 187, 187A Belden 9221	Go/c	Front-Gold Rear-Nickel	TEFLON	Mil Type	—	414075-2
		Go/c	Nickel	TEFLON	Mil Type	414767-1	414075-6

Tooling—Page 134

[†]Refer to pages 14 and 15 for cable code specifications.