


Dimensions: mm (In.)

**Mechanical Specifications:**

- Operating Frequency: 300 operations/min.
- Mechanical Life : 5,000,000 operations(Min.)

Note:

- RoHS compliant and process compatible with 260° solder.

Electrical Specifications:

- Insulation Resistance (at 500VDC): 100M Ω Min.
- Dielectric Strength: 1,000VAC RMS(50-60HZ)
- Contact Resistance (Initial): 30m Ω Max.
- Operating Frequency: 10-30 operations/min.
- Operating Speed: 0.1mm to 1m/sec.
- Electrical Life: 6,000~100,000 operations(Min.)
- Rating: 10.1A/125/250 VAC

Operating Characteristics:

- OF (g) max: 75
- OP (mm): 15.0 $\pm$ 1.5
- PT max: 4.80mm
- OT min (mm): 1.0
- MD max (mm): 2.70

Miniature Snap Switch
101-73-10-075ST-EV

**Mountain
Switch**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[101-73-10-075ST-EV](#)