

Current refinements (click  to remove)

[Search Tips](#) 
 [Region](#)  [USA](#)  [Product Family](#)  [Flex Conductor, One-Hole, Standard Barrel with Window Lug](#)  [Text Search: 'LCAX2-38-E'](#)


For Use with Flexible, Extra-Flexible, and Code Stranded Copper Conductors

- Can be used with code conductor and flex conductor class: G, H, I, K, M and Diesel Locomotive
- Generously beveled wire entry prevents bent back strands when inserting conductor into barrel
- Color-coded barrels marked with **PANDUIT** and specified competitor die index numbers for proper crimp die selection
- Inspection window to visually assure full conductor insertion
- Tin-plated to inhibit corrosion
- UL Listed and CSA Certified to 35 KV** and temperature rated to 90°C when crimped with **PANDUIT** and specified competitor crimping tools and dies
- American Bureau of Shipping Approved

Related Products

[Contour Crimp™ Control...](#)
[Die Type, Battery Powered Hydraulic...](#)
[Die Type, Battery Powered Hydraulic...](#)
[CD-2001 Crimping Dies](#)
[Die Type, Manual Hydraulic, 14 Ton,...](#)
[Die Type, Remote Hydraulic, 14 Ton,...](#)
[More...](#)

Part Number:	LCAX2-38-E
RoHS Compliancy Status:	Compliant
Part Description:	Flex Lug, #2 AWG, 3/8" Stud Hole
Length (In.):	1.70
Length (mm):	43.2
Class G,H, I, K, M:	#2 AWG
Diesel Locomotive:	#2 AWG
Stud Hole Size (In.):	3/8
Tongue Width (In.):	.70
Barrel Length (In.):	.59
Angle:	Straight
Figure No.:	1
Panduit Color Code:	Brown
Panduit Die Index No.:	P33
Tongue Thickness:	.11
Tongue Type:	Standard
Tongue Width (mm):	17.8
Wire Strip Length (In.):	11/16
Min. Order UOM:	PC
Min. Order Qty.:	1
Burndy Die Index No.:	10
T&B Die Index No.:	33
BOM Qty. (# of Pkgs.)	

Add to My Catalog



Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

Material	High Conductivity Seamless Copper Tube
Plating	Electro-Tin
Wire Size	2 STR/FLEX
Wire Type	Stranded Copper: Class B & C, Compact, Class G, H, I, K, M, Locomotive
Wire Strip Length	11/16 in.
Stud Size	3/8 in.
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.
UL Temperature Rating	90° C
C.S.A Certified Wire Connector	Yes
Panduit Color Code on Barrel	BROWN
Panduit Die Index No. on Barrel	P33
Alternate Industry Die Index No. () on Barrel	(10)



LISTED
Wire Connector



00	6/03	CJW	SAC	RELEASED	10850	PANDUIT CORP. TINLEY PARK, ILLINOIS	
REV	DATE	BY	CHK	DESCRIPTION	ECN	SCALE	DRAWING NO / CAD FILE
						N/A	LCAX2-38-CUST

PANDUIT

CORP. TINLEY PARK, ILLINOIS

LCAX2-38-E

Copper Lug - One-Hole, Standard Flex Barrel

SCALE
N/A

DRAWING NO / CAD FILE

LCAX2-38-CUST