


OGA DIAGONAL: 20.98 [532.86]
VA DIAGONAL: 20.27 [514.90]
PA DIAGONAL: 19.11 [485.30]

SKU 98 NUMBER	TYPE	DIM "A" (TOTAL GLASS TO CONNECTOR)	A/G FINISH	PROD SPEC
98-0003-3547-5	USB R	4.27" [108.46]	AG500	23655



ESD CLAMSHELL CASE




USB R
EXII-7760UC
98-0003-2814-0
USB CONTROLLER
SOLDER SIDE

PIN #1
SEE NOTE 2

"A"
± .060 [1.52]
REF

.147±.020 [3.73±.51]
TOTAL THICKNESS
OF GLASS, CABLE
AND STRAIN RELIEF



.125
[3.18]
REF

NOTES:

1. WEIGHT OF GLASS IN GRAMS: 936±10%

PINOUT	
1	LR
2	LL
3	SHIELD
4	UL
5	UR

UNITS INCHES [MM]	
TOLERANCES UNLESS OTHERWISE SPECIFIED	
.X	± .03 [.76]
.XX	± .015 [.38]
.XXX	± .015 [.38]
ANGLES	± 1°
THIRD ANGLE PROJECTION	
DO NOT SCALE DRAWING	
SCALE 1 = 1	
3M 3M TOUCH SYSTEMS METHUEN, MA USA	
© COPYRIGHT 2005 THIS DOCUMENT IS COPYRIGHTED PROPERTY OF THE 3M COMPANY AND MAY NOT BE REPRODUCED WITHOUT 3M WRITTEN PERMISSION OR USED OR DISCLOSED FOR OTHER THAN 3M AUTHORIZED PURPOSES.	
DRAWN	MTD 12/22/09

01	RELEASE PER CO 031235	12/09	MTD
REV	CHANGE NOTICE	DATE	DRW
MARKETING DRAWING			
SCT32NN 20.27" W			
CAD FORMAT	AUTOCAD	SHEET	1 OF 1
SIZE	DOCUMENT NO.	REV	
C	37514-MKT		01