


REV	DOCUMENT	CHANGED BY	CHECK
A	0063827	LK	06MAY10 CMH

HONEYWELL PART NUMBER
WAN05RSP
PRODUCT CODE
WSC0007



NOTES:

1 - RoHS & REACH COMPLIANT.
 2 - PROTECT AGAINST DIRECT RAIN, SALT, SNOW, ICE, ETC.

ELECTRICAL SPECIFICATIONS	
FREQUENCY	2.4 GHz
GAIN	9.0 dBi
IMPEDANCE	50 OHMS
VSWR	<1.5 TYP. AT CENTER

MECHANICAL SPECIFICATIONS	
OPERATING TEMPERATURE	-40°C TO +60°C
CONNECTOR TYPE	RP-SMA PLUG
ANTENNA MATERIAL	UV STABLE MOLDED POLYURETHANE
INDOOR/LIMITED OUTDOOR EXPOSURE	YES
RoHS COMPLIANT	YES
APPROX. WEIGHT	2.1oz (60gm)

A DESIGN UNITS: INCH
 TOLERANCES UNLESS NOTED:

NO PLACES	X	±	.400
ONE PLACE	.X	±	.03
TWO PLACE	.XX	±	.015
THREE PLACE	.XXX	±	.005
ANGLES	X	±	3°

THIRD ANGLE PROJECTION



DRAWN	SJK	19APR10
CHECK	VK	19APR10

THIS DRAWING COVERS A PROPRIETARY ITEM
 AND IS THE PROPERTY OF HONEYWELL.
 THIS DRAWING IS NOT TO BE COPIED OR USED
 WITHOUT THE PERMISSION OF HONEYWELL.

INTERPRET PER ASME Y14.5M-1994
 OTHER HONEYWELL ENGINEERING
 STANDARDS MAY APPLY

Pro/ENGINEER

SIZE	TYPE	CAGE CODE	DRAWING NAME	REV
A	I	-	WAN05RSP	A

3D

SCALE 1:2

SHEET 1 OF 1

Honeywell

TITLE 9.0dBi ANTENNA, OMNI-DIRECTIONAL,
 TILT/SWIVEL