


Features

- Broad Frequency Range
- Fully Hermetic Package (HHS-110)
- High Isolation: Typically 30 dB
- Impedance: 50 Ohms Nominal
- Input Power: 1 Watt Maximum
- MIL-STD-202 Screening Available


Description

3 dB Hybrids are ideal for dividing a signal into two signals of equal amplitude and a constant 90° or 180° phase differential and for Quadrature combining or performing summation/differential combining.


SF-1 (HHS-110)



FP-2 (HH-110)



TO-8-2 (HH-127)



Electrical Specifications¹: $T_A = -55^{\circ}\text{C}$ to $+85^{\circ}\text{C}$

Parameter	Test Conditions	Frequency	Units	Min	Typ	Max
Insertion Loss	Less Coupling	10 - 500 MHz	dB	—	—	1.4
		25 - 200 MHz	dB	—	—	1.0
Isolation		10 - 500 MHz	dB	20	—	—
		25 - 200 MHz	dB	30	—	—
Amplitude Balance		10 - 500 MHz	dB	—	—	0.6
		25 - 200 MHz	dB	—	—	0.4
VSWR		10 - 500 MHz	Ratio	—	—	2.0:1
		25 - 200 MHz	Ratio	—	—	1.6:1
Phase Balance		10 - 500 MHz	°	—	—	7
		25 - 200 MHz	°	—	—	5

1. All specifications apply with 50 ohm source and load impedance.

Pin Configuration (HH-110)

Pin No.	Function	Pin No.	Function
1	A	5	B
2	GND	6	GND
3	GND	7	GND
4	C	8	D


Pin Configuration (HHS-110)

Pin No.	Function	Pin No.	Function
1	A	3	B
2	C	4	D

Pin Configuration (HH-127)

Pin No.	Function	Pin No.	Function
1	GND	7	GND
2	C	8	B
3	GND	9	GND
4	GND	10	GND
5	A	11	D
6	GND	12	GND

Functional Diagram



M/A-COM Inc. and its affiliates reserve the right to make changes to the product(s) or information contained herein without notice. M/A-COM makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does M/A-COM assume any liability whatsoever arising out of the use or application of any product(s) or information.

Visit www.macom.com for additional data sheets and product information.


■ **North America:** Tel. (800) 366-2266
 ■ **Asia/Pacific:** Tel.+81-44-844-8296, Fax +81-44-844-8298
 ■ **Europe:** Tel. +44 (1344) 869 595, Fax+44 (1344) 300 020

tyco / Electronics


M/A-COM

Typical Performance Curves


Insertion Loss



Isolation



VSWR



Ordering Information

Part Number	Package
HH-110 PIN	FP-2
HHS-110	SF-1
HH-127 PIN	TO-8-2

M/A-COM Inc. and its affiliates reserve the right to make changes to the product(s) or information contained herein without notice. M/A-COM makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does M/A-COM assume any liability whatsoever arising out of the use or application of any product(s) or information.

Visit www.macom.com for additional data sheets and product information.

■ North America: Tel. (800) 366-2266
■ Asia/Pacific: Tel.+81-44-844-8296, Fax +81-44-844-8298
■ Europe: Tel. +44 (1344) 869 595, Fax+44 (1344) 300 020