

## Non-Adhesive Continuous Tag Stock (B-551)

For safety, lockout and general purpose hang-tagging.

- Non-adhesive, semi-rigid tag stock
- Easy to hole-punch; optional snap-in grommets available
- Meets OSHA 50 lb. pullout spec for lockout tags

Service temp: -40°F to 193°F Average Outdoor Durability: up to 2 years  
Thickness: 0.35mm



| Fits Printer Model(s) | Diagram | Catalog #        | Color | Label Width A Inch (mm) | Roll Length B Inch (mm) | Tags Per Roll         | Rec. Ribbon |
|-----------------------|---------|------------------|-------|-------------------------|-------------------------|-----------------------|-------------|
| BBP31, BBP33          | Fig. 33 | B30C-2500-551-WT | White | 2.500 (63.5)            | 50ft. (15.2m)           | - continuous supply - | B30-R10000  |
| BBP31, BBP33          | Fig. 33 | B30C-3250-551-WT | White | 3.250 (82.6)            | 50ft. (15.2m)           | - continuous supply - | B30-R10000  |
| BBP31, BBP33          | Fig. 33 | B30C-4250-551-WT | White | 4.250 (107.9)           | 50ft. (15.2m)           | - continuous supply - | B30-R10000  |

Figure 33



## Retro Reflective Tape (B-584)

For highly reflective identification that shines back brightly when struck by light.

- Ideal for labeling outdoor utility poles and pedestals, jobsite equipment and roof-top equipment
- Recommended for low light or inclement weather conditions

Service temp: -40°F to 158°F  
Application temp: 0°F to 158°F (yellow & orange), 50°F to 158°F (silver)  
Average Outdoor Durability: 4 to 6 years




Figure 33



| Fits Printer Model(s) | Diagram | Catalog #        | Color  | Label Width A Inch (mm) | Roll Length B Inch (mm) | Labels Per Roll       | Rec. Ribbon |
|-----------------------|---------|------------------|--------|-------------------------|-------------------------|-----------------------|-------------|
| BBP31, BBP33          | Fig. 33 | B30C-1125-584-SL | Silver | 1.125 (28.6)            | 50ft. (15.2m)           | - continuous supply - | B30-R10000  |
| BBP31, BBP33          | Fig. 33 | B30C-2250-584-SL | Silver | 2.250 (57.5)            | 50ft. (15.2m)           | - continuous supply - | B30-R10000  |
| BBP31, BBP33          | Fig. 33 | B30C-4000-584-SL | Silver | 4.000 (101.6)           | 50ft. (15.2m)           | - continuous supply - | B30-R10000  |
| BBP31, BBP33          | Fig. 33 | B30C-1125-584-YL | Yellow | 1.125 (28.6)            | 50ft. (15.2m)           | - continuous supply - | B30-R10000  |
| BBP31, BBP33          | Fig. 33 | B30C-2250-584-YL | Yellow | 2.250 (57.5)            | 50ft. (15.2m)           | - continuous supply - | B30-R10000  |
| BBP31, BBP33          | Fig. 33 | B30C-4000-584-YL | Yellow | 4.000 (101.6)           | 50ft. (15.2m)           | - continuous supply - | B30-R10000  |
| BBP31, BBP33          | Fig. 33 | B30C-1125-584-OR | Orange | 1.125 (28.6)            | 50ft. (15.2m)           | - continuous supply - | B30-R10000  |
| BBP31, BBP33          | Fig. 33 | B30C-2250-584-OR | Orange | 2.250 (57.5)            | 50ft. (15.2m)           | - continuous supply - | B30-R10000  |
| BBP31, BBP33          | Fig. 33 | B30C-4000-584-OR | Orange | 4.000 (101.6)           | 50ft. (15.2m)           | - continuous supply - | B30-R10000  |

## BradyGlo™ High-Intensity Photoluminescent Tape (B-526)

For glow-in-the-dark identification up to 10 hours!

- Designed for directional and evacuation marking
- Ideal for marking emergency utility shut-offs, fire extinguishers, alarm pulls, and vital equipment controls
- Complies with indoor use requirements specified in RS 6-1 and 6-1A of New York Local Law 26

Service temp: -40°F to 140°F Application temp: 40°F to 140°F



| Fits Printer Model(s) | Diagram | Catalog #     | Color          | Label Width A Inch (mm) | Roll Length B Inch (mm) | Labels Per Roll       | Rec. Ribbon |
|-----------------------|---------|---------------|----------------|-------------------------|-------------------------|-----------------------|-------------|
| BBP31, BBP33          | Fig. 33 | B30C-1125-526 | Luminous Green | 1.125 (28.6)            | 50ft. (15.2m)           | - continuous supply - | B30-R10000  |
| BBP31, BBP33          | Fig. 33 | B30C-2250-526 | Luminous Green | 2.250 (57.5)            | 50ft. (15.2m)           | - continuous supply - | B30-R10000  |
| BBP31, BBP33          | Fig. 33 | B30C-4000-526 | Luminous Green | 4.000 (101.6)           | 50ft. (15.2m)           | - continuous supply - | B30-R10000  |

Figure 33

