




General ordering data

Order No.	1041620000
Part designation	WDK 2.5N PE
Version	Earth terminal, 2.5 mm ² , Screw connection, Wemid, green/yellow, TS 35
EAN	4032248138579
Qty.	100 pc(s).

Product notes

Note, technical data	2.5 mm ² conductor with wire end ferrule plus plastic collar only with collar optimised for diameter (order No. 1333100000, 500 pcs)
Product description	Their small size compared to the respective rated cross-section makes the modular terminals with the compact design very popular.
Note, accessories	Rail support for insulated installation of terminal rail "SH 2" order no. 0494920000 (10 pcs)

PT OKIECEEx/ATEX rating data

EU-type examination certificate	KEMA00ATEX2061U
Download, German	KEMA00ATEX2061U_d.pdf
Download English	KEMA00ATEX2061U_e.pdf
IECEEx Certificate of Conformity	IECEXULD05.0008U
Download	IECEXULD05.0008U_e.pdf
ATEX conductor cross-section	2.5 mm ²
IECEEx conductor cross-section	2.5 mm ²
Voltage when using cross-connections	CrossConnectionGuide.pdf
Operating temperature range	For operating temperature range see EC Design Test Certificate / IEC Ex-Certificate of Conformity
Marking EN 60079-7	Ex e II
Marking ATEX Directive 94/9/EC	Ex II 2 G D

Additional technical data

Colour of insulating material	green/yellow
Connection direction	on side

Additional technical data

End plate required	Yes
Explosion-tested version "Ex e"	Yes
Installation advice	TS 35
Insulating material	Wemid
Levels cross-connected internally	Yes
No. of identical terminals	1
No. of levels	2
No. of terminal strips per level	2
Open sides	right
Operating temperature range	- 50 °C, + 120 °C
Product family	W-Series
Type of connection	Screwed
Type of mounting	Snap-on
UL 94 flammability rating of insulation material	V-0
Version	PE terminal

CSA rating data

Min. cross-section (CSA)	AWG 26
Max. cross-section (CSA)	AWG 12

Conductors for clamping (rated connection)

Clamping range, min.	0.05 mm ²
Clamping range, max.	4 mm ²
Type of connection	Screw connection
2nd type of connection	screwed
Connection direction	on side
No. of connections	4
Stripping length	8 mm
Clamping screw	M 2.5
Blade size	0.6 x 3.5 mm
Tightening torque range	0.4...0.6 Nm
Torque level with DMS electric screwdriver	1
Gauge to IEC 60947-1	A3
Solid, min.	0.5 mm ²
Solid, max.	4 mm ²
Stranded, min.	1.5 mm ²
Stranded, max.	4 mm ²
Flexible, min.	0.5 mm ²
Flexible, max.	4 mm ²
Flexible with ferrule, min. (DIN 46228/1)	0.5 mm ²
Flexible with ferrule, max. (DIN 46228/1)	2.5 mm ²
Flexible, min., ferrule with plastic collar (DIN 46228 pt 4)	0.5 mm ²
Flexible, max., ferrule with plastic collar (DIN 46228 pt 4)	2.5 mm ²
AWG conductor size, min.	AWG 26
AWG conductor size, max.	AWG 12
AWG conductor size, min.	0.13 mm ²
AWG conductor size, max.	3.31 mm ²

Dimensions

Width	5.1 mm
Height of lowest version	62.5 mm
Length	60.7 mm
TS 35 offset	30.85 mm

Disconnect terminals

Torque level with DMS electric screwdriver	1
--	---

PE rating data

PEN function	No
Pollution severity	3
Rated cross-section	2.5 mm ²
Rated impulse withstand voltage to adjacent terminal	8 kV
Rated short-time current	300 A (2.5 mm ²)
Rated voltage for adjacent terminal	800 V
Standards	IEC 60947-7-2
Torque level with DMS electric screwdriver	1

UL rating data

Min. cross-section (UL)	AWG 30
Max. cross-section (UL)	AWG 12

Approvals

Approvals institutes



Classifications

eClass 4.1	27-14-03-05
eClass 5.0	27-14-03-05
eClass 5.1	27-14-03-05

Similar products

Order No.	Part designation	Version
1016200000	WPE 2.5N	Earth terminal, 2.5 mm ² , Screw connection, Wemid, green/yellow, TS 35
1042700000	WPE 4N	Earth terminal, 4 mm ² , Screw connection, Wemid, green/yellow, TS 35
1041920000	WDK 4N PE	Earth terminal, 4 mm ² , Screw connection, Wemid, green/yellow, TS 35

1019100000	WPE 16N	Earth terminal, 16 mm ² , Screw connection, Wemid, green/yellow, TS 35
1717740000	WPE 35N	Earth terminal, 35 mm ² , Screw connection, Wemid, green/yellow, TS 35
1846040000	WPE 50N	Earth terminal, 50 mm ² , Screw connection, Wemid, green/yellow, TS 35
9512200000	WPE 70N/35	Earth terminal, 70 mm ² , Screw connection, Wemid, green/yellow, TS 35
1846030000	WPE 95N/120N	Earth terminal, 95 mm ² , Screw connection, Wemid, green/yellow, TS 35