

フラット防水リフトハンドル

WATERPROOF FLUSH LIFT HANDLES



A-212

ギア式

平面
ハンドル

ポップ
ハンドル

リフト
ハンドル

アジャスト
ハンドル

ラッチ式

スナッチ

リンク

フック式

ロック
ハンドル

L型
ハンドル

T型
ハンドル

丸型
小型

押ボタン

取手

つまみ

止め金
ロッド棒

ジョイント
リンク

ワイヤ

総合 21

331




A-212-3

PAT.PEND.



キーNo.0200
Key



特徴 Feature

- ハンドルを収納することにより止め金が3~5mmリフト。シールド効果が得られます。
- 指でハンドルをリフトさせるシンプル構造です。
- 防水タイプ(Oリング・シートパッキン使用)
- 左右兼用型
- The stopper plate will be lifted up 3 to 5mm when the handle is encased in the housing, providing excellent sealing effects.
- It is a simple construction that the handle is lifted up by finger.
- Waterproof (using O-ring and sheet packing)
- For both left-hand and right-hand use.

仕様

- 材質:亜鉛合金(ZDC)
- 表面仕上:サチライクロムめっき(MZCr)
- 鍵番号:0200
- 付属品:キー2本・ビスセット・専用止め金

用途

- 情報通信機器(デジタル装置・磁気ディスク装置)などのEMI防止用シールドラック
- 標準品・・・即納します

納期備考

- 鍵の回転角度は360°となります。必要以上に回転させると錠前部・鍵先端部が破損する恐れがありますのでご注意下さい。
- 本製品の錠前はキー先端部での操作となります。

Specifications

- Material: Zinc alloy (ZDC)
- Finish: Satellite chrome plating (MZCr)
- Key No.: 0200
- Accessories: Two keys, screws and special stopper plate

Specific use

- EMI-proof sealed racks for data communication equipment (digital and magnetic disc equipment)

Remarks

- The rotation angle of the key is 360°. If turned more than necessary the lock or the tip of the key can be damaged, so care is required.
- The lock on this product is operated with the tip of the key.

