



LOC	DIST	REVISIONS					
CE	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B1	REVISED PER ECO-11-005027	29APR11	RK	HMR

PERFORMANCE REQUIREMENTS:	
OPERATING WAVELENGTH	: 1310/1550 ±25nm
REFLECTANCE	: ≤ -55dB
OPERATING TEMPERATURE	: -40°C TO +75°C
ATTENUATION TOLERANCE, AMBIENT	:
FOR 0 dB ATTENUATORS	: + 0.50dB MAX
FOR ATTENUATORS ≤ 5dB	: ± 0.50dB
FOR ATTENUATORS >5dB	: ± 10% OF NOMINAL ATTENUATION VALUE
MEASURED WITH REFERENCE QUALITY LAUNCH LEADS	



SCALE 3:1



NOMINAL ATTENUATION VALUE (dB)	PART NUMBER
0	9-5209943-9
1	5209943-1
2	5209943-2
3	5209943-3
4	5209943-4
5	5209943-5
6	5209943-6
7	5209943-7
8	5209943-8
9	5209943-9
10	1-5209943-0
11	1-5209943-1
12	1-5209943-2
13	1-5209943-3
14	1-5209943-4
15	1-5209943-5
16	1-5209943-6
17	1-5209943-7
18	1-5209943-8
19	1-5209943-9
20	2-5209943-0
25	2-5209943-5

△ TYCO LOGO, ATTENUATION VALUE, PART NUMBER, AND SERIAL NUMBER ARE PRINTED ON THE LABEL.

DIMENSIONS: mm[INCHES]		DWN E. HOPKINS 05DEC2005		 TE Connectivity	
		CHR E. HOPKINS 05DEC2005			
		APVD S. BUCHTER 05DEC2005		NAME ATTENUATOR, FOPC BOA SC/UPC DW SM	
		PRODUCT SPEC -			
MATERIAL -		APPLICATION SPEC -		SIZE A2	
		WEIGHT -		CAGE CODE 00779	
DIMENSIONS: mm[INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DRAWING NO C-5209943	
DIMENSIONS: mm[INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		RESTRICTED TO -	
DIMENSIONS: mm[INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		SCALE 1:1	
DIMENSIONS: mm[INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		SHEET OF	
DIMENSIONS: mm[INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		REV B1	