

## Ferrule - A 25 -12 - 3200357

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Ferrule, Length: 12 mm, Color: silver

The figure shows variant A 1-6

### Product Features

- ✓ The A 0,25.. ferrules can also be used to process 0.14 mm<sup>2</sup> conductors
- ✓ The dimensions of the ferrules conform to DIN 46228-1
- ✓ The ferrules without plastic sleeve are made from soft tin-plated electrolytic copper

### Key commercial data

|                                      |                                                                                                         |
|--------------------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit                         | 1 1                                                                                                     |
| Minimum order quantity               | 100 1                                                                                                   |
| GTIN                                 | <br>4 017918 094003 |
| Weight per Piece (excluding packing) | 0.56 GRM                                                                                                |
| Custom tariff number                 | 85369010                                                                                                |
| Country of origin                    | Germany                                                                                                 |

### Technical data

#### Dimensions

|                                              |        |
|----------------------------------------------|--------|
| Length (b)                                   | 12 mm  |
| Sleeve length                                | 10 mm  |
| Inner dimension of the insulating collar (d) | 9.5 mm |
| Ferrule diameter                             | 7.3 mm |
| Sleeve wall thickness                        | 0.2 mm |

#### Ambient conditions

|                            |        |
|----------------------------|--------|
| Max. permanent temperature | 105 °C |
|----------------------------|--------|

#### General

|      |                                                         |
|------|---------------------------------------------------------|
| Note | These ferrules are not included in DIN 46228-1: 1992-08 |
|------|---------------------------------------------------------|

# Ferrule - A 25 -12 - 3200357

## Technical data

### General

|          |        |
|----------|--------|
| Color    | silver |
| Material | E-CU   |

## Classifications

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27060701 |
| eCl@ss 4.1 | 27060701 |
| eCl@ss 5.0 | 27400201 |
| eCl@ss 5.1 | 27400201 |
| eCl@ss 6.0 | 27400201 |
| eCl@ss 7.0 | 27400201 |
| eCl@ss 8.0 | 27400201 |

### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000005 |
| ETIM 3.0 | EC000005 |
| ETIM 4.0 | EC000005 |
| ETIM 5.0 | EC000005 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30212109 |
| UNSPSC 7.0901 | 27121703 |
| UNSPSC 11     | 27121703 |
| UNSPSC 12.01  | 27121703 |
| UNSPSC 13.2   | 27121703 |

## Approvals

### Approvals

#### Approvals

CSA / CSAus / cCSAus

#### Ex Approvals

## Ferrule - A 25 -12 - 3200357

### Approvals

Approvals submitted

---

#### Approval details

CSA 

CSAus

cCSAus

---