



## Shrink-Kon®

### CMP1000-0-A

Dual listed CSA / UR flexible heat shrink tubing.

<b>T&amp;B Catalog Number:</b>	<b>CMP1000-0-A</b>
<b>EAN Number:</b>	05414363102199
<b>UPC Number:</b>	78621082339
<b>Description:</b>	CMP thin wall dual listed UL/CSA heat shrink tubing, with expanded diameter 25.4 mm, black, shrink ratio 2:1, length 12.2 m (10 x 1.22m)



#### Technical Information

Tubing Family	CMP
Wall Thickness	thin
Shrink Ratio	2:1
Tube Characteristics	single wall
Material	PE crosslinked polyolefin
Temperature Range	-55°C to +125°C
Shrink Temperature	> +110°C
IP Rating	IP60
Flammability Rating	self-extinguishing
Colour	black
Silicone free	yes
Lead/Cadmium free	yes
Dielectric Strength	20 KV/mm
Chemical Resistance	very good

#### Approvals

UL recognised	E79546
CSA approved	702106

#### Ordering Information

Expanded Diameter as Supplied (inch)	1
Expanded Diameter as Supplied (mm)	25.4
Fully Recovered Diameter (mm)	12.7
Wall Thickness before Shrinking (mm)	0.45
Wall Thickness after Shrinking (mm)	0.8

Length (m)	12.2
Quantity per Box (pieces of 1.22 m)	10
Packaging Type	box