


Terminal Block Plugs

158-P022ESDVP, 158-P032ESDVP, 158-P042ESDVP, 158-P052ESDVP,
158-P062ESDVP, 158-P072ESDVP, 158-P082ESDVP, 158-P092ESDVP,
158-P102ESDVP, 158-P112ESDVP, 158-P122ESDVP



Terminal Block Plugs

158-P022ESDVP, 158-P032ESDVP, 158-P042ESDVP, 158-P052ESDVP, 158-P062ESDVP, 158-P072ESDVP,
158-P082ESDVP, 158-P092ESDVP, 158-P102ESDVP, 158-P112ESDVP, 158-P122ESDVP



Dimensions: mm (In.)

P	02P	03P	04P	05P	06P	07P	08P	09P	10P	11P	12P
U mm	5.08	10.06	15.24	20.32	25.40	30.48	35.58	40.64	45.72	50.80	55.88
V mm	10.16	15.24	20.32	25.40	30.48	35.56	40.64	45.72	50.80	55.88	60.16

ELECTRICAL SPECIFICATIONS

Rating:	300V 15A
Pitch:	5.08 mm
Insulation withstands voltage:	AC 1500V/Min
Insulation resistance:	500MΩ or more at DC500V
Temperature range:	-40°C ~ +105°C
Screw torque value:	5kg - cm
Electric wire:	28 ~ 12 AWG

MATERIAL SPECIFICATIONS

Screw (5):	Steel, M2.5 Zinc Plated
Wire cage (4):	Steel, Zinc Plated
Clamp (3):	Phosphor Bronze, Solder Plated
Cover (2):	PA66, Green
Housing (1):	PA66, Green

Date Last Revised: 10-18-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC- 300771

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[158-P022ESDVP](#) [158-P112ESDVP](#) [158-P032ESDVP](#) [158-P062ESDVP](#) [158-P122ESDVP](#)