


REVISIONS		DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398				
DCP #	REV	DESCRIPTION		DRAWN DATE	CHECKD DATE	APPRVD DATE
1878	A	RELEASED		EO 05/02/06	YA 6/19/06	HO 6/19/06


Specifications:

- Rated Voltage: 300V
- Rated Current: 15A
- Wire Range: 22 ~ 12 AWG
- Test Voltage: 4kV
- Rated Torque: 0.5 Nm
- Screw Size: M3
- Wire Stripped Length: 6.0 mm
- Insulating Material: PA
- Flammability Class: UL94V-0
- Temperature Range: -30°C to +105°C
- Block Material: CuZn, Green Color
- Wire Guard Material: CuSn

TOLERANCES:	DRAWN BY:	DATE:	DRAWING TITLE: Terminal Block, Pluggable, Cage Clamp, Horizontal Plug			
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.	EKLAS ODISH	05/02/06	SIZE	DWG. NO.	ELECTRONIC FILE	REV
	YILMAZ AKYONDEM	6/19/06	A	TA-765	TA-765.DWG	A
	APPROVED BY:	DATE:	SCALE:	NTS	U.O.M.: Millimeters	SHEET: 1 OF 1
	HISHAM ODISH	6/19/06				

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED
HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE
BELIEVE TO BE ACCURATE AND RELIABLE. SINCE
CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE
USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT
FOR THE INTENDED USE AND ASSUME ALL RISK AND
LIABILITY WHATSOEVER IN CONNECTION THEREWITH.