

Our new 2012 models have arrived!

Home > VIERA Televisions > VIERA 3D HDTVs > TC-P50GT30

VIERA® 50" Class GT30 Series Plasma HDTV with 3D (49.9" Diag.)

Model number: TC-P50GT30

User Review 4.6

Read Customer Reviews Write a review

[Print this](#) | [Share this](#)

- Full HD 3D
- Flush Design
- Infinite Black 2 Panel
- VIERA Connect WiFi Ready

Available at your favorite retailer



[watch tutorial](#) [see video](#) [download specs](#) [enlarge](#)



- Overview
- Tech Specifications
- Reviews
- FAQs
- Accessories
- Operating Manuals
- Warranty & Care Plans

Screen Size Diagonal (inches)	49.9
Aspect Ratio	16:9
Native Resolution (Number of Pixels)	2,073,600 (1,920 x 1,080)
Moving Picture Resolution	1080 lines
Shades of Gradation	6,144 equivalent
HDTV Display Capability (1080p, 1080i, 720p)	Yes
EDTV Display Capability (480p)	Yes
Aspect Control	4:3, Zoom, Full, Just, H-fill for TV/AV modes 4:3, Full for PC mode
Louver Filter	Yes
600Hz Sub-field Drive	Yes
24p Playback (2 : 3)	Yes
Deep Color	Yes
x.v.Color	Yes
Super Resolution	Yes
Pro Setting	Yes
THX Mode	Y (3D/2D)
3D Color Management	Yes
Sub Pixel Control	Yes
Motion Pattern Noise Reduction	Yes
3D Panel	Yes
3D 24p Cinema Smoother	Yes
2D-3D Conversion	Yes
3D Image Viewer	Yes
Speakers	Full-range x 2 (L, R)
Number of Speakers	2
Audio Output	20 W
Surround Sound	Yes
Integrated ATSC Tuner	Yes
VIERA Image Viewer™	Y (AVCHD/MPEG2/JPEG/MP3 playback)
HDMI Input	4 (4 side)
Composite Video Input	RCA x 1 (lower) (with special adapter cable (dedicated))
PC Input	D-sub 15-pin x 1 (rear) (with special adapter cable (dedicated))
Component Video Inputs (Y, PB, PR)	RCA x 1 (lower) (with special adapter cable (dedicated))
Audio Input (for Component Video)	RCA x 1 (lower) (with special adapter cable (dedicated))
Digital Audio Output (Optical)	1 (with special adapter cable (dedicated))
HDMI Input-Support Feature	Audio Return Channel (Input 1) / 3D Input (All)
Analog Audio Input (for HDMI/DVI)	Yes
USB	3
LAN Port	1
VIERA Link™	Yes
VIERA Connect (IPTV)	Yes
VIERA® Tools	Yes
Game Mode	Yes
3D Active Shutter Eyewear	Not Included
Pixel Orbiter (Anti-Image Retention)	Yes
Menu Languages	English/Spanish/French
Built-In Closed Caption Decoder	Yes
Off - Timers	Yes
Wireless LAN Adaptor	Yes
DLNA	Yes
Power Supply	AC 120 V, 60Hz
Receiving System	ATSC/QAM/NTSC
Operating Temperature	32°F - 104°F (0°C - 40°C)
Safety Standard	UL60065 (7th generation)/C-UL
Swivel Angle	+10°
Optional Wall-mounting Bracket	TYWK4P1RW
Dimensions (H x W x D) with Stand	29.7" x 46.4" x 13.2"
Dimensions (H x W x D) without Stand	28.3" x 46.4" x Speaker depth: 2.3"; Panel depth: 1.5"
Weight (lbs.) w/Stand	65.1 lbs.
Weight (lbs.) without Stand	56.3 lbs.
Carton Dimensions (H x W x D)	32.9" x 53.0" x 10.0"

You may also like



VIERA65" Class GT30 Series Plasma HDTV with 3D (64.7" Diag.)

(8 Reviews)

Suggested Retail Price: ~~\$3,499.96~~
Less: \$799.99
Your Price: \$2,399.96

TC-P65GT30

[LEARN MORE](#)



VIERA65" Class ST30 Series Plasma HDTV with 3D (64.7" Diag.)

(18 Reviews)

Suggested Retail Price: ~~\$2,999.96~~
Less: \$749.99
Your Price: \$2,249.96

TC-P65ST30

[LEARN MORE](#)

Need assistance with your order?

- [Email click here](#)
- Call** 1-800-405-0652
Mon-Fri 8:00 AM - 9:00 PM EST
Sat-Sun 12:00 PM - 5:00 PM EST
- [Live Chat click here](#)

Recently Viewed Products



VIERA® 42" Class X3 Series Plasma HDTV (41.6" Diag.)

5 Reviews

TC-P42X3