





- 1 WIRE SIZE IS [#18-#14] AWG.
- 2 INSULATION RANGE IS 2.79-4.57[.110-.180] DIA.
2.79-3.56 [.110-.140] DIA - CRIMP WIDTH 4.57 [.180], F TYPE
3.56-4.57 [.140-.180] DIA - CRIMP WIDTH 4.57 [.180], O TYPE
- 3 MATING TAB THK TO BE 0.51±0.025[.020±.001]



SECTION X-X
SCALE 10:1



SECTION Y-Y
SCALE 10:1

0.001016 [.000040] MIN TIN		521271-2				
-		521271-1				
TERMINAL / MATERIAL		PART NO.				
DWN JR RUTH CHK MS FEHER APVD J HUMMEL	24FEB00 24FEB00 24FEB00	 TE Connectivity				
PRODUCT SPEC						
-		ASSEMBLY, RECEPT, POSI-LOCK, ULTRA-POD, 4.75 [.187] SERIES				
APPLICATION SPEC						
-						
WEIGHT -		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
		A2	00779	C-521271	-	
CUSTOMER DRAWING				SCALE 5:1	SHEET 1 OF 1	REV E