


Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

FCI

FCI P/N (NOTE 1)	LENGTH (NOTE 1)
57663-YXXX	XXX



NOTES:

1. FCI P/N CONSISTS OF THE DWG NO, A DASH A SUFFIX Y AND A SUFFIX XXX WHERE Y IS THE UNIT OF LENGTH(Y=M IS METERS AND Y=F IS FEET) AND WHERE XXX IS THE LENGTH "L".
(EX. 57663-F004 IS 4 FT IN LENGTH)

SPECIFICATIONS		
	FC2	FC/APC
INSERTION LOSS	0.5dB MAX	0.5dB MAX
RETURN LOSS	55dB MIN	60dB MIN
FIBER PROTRUSION	50nm MAX	50nm MAX
APEX OFFSET	45um MAX	45um MAX
FIBER UNDERCUT	SEE TELECORDIA GR-326	

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY	Electronics FCI www.fciconnect.com		
ltr	ecn no	dr	date	linear	NOMINALS ONLY				
A	V11336	JJK	5/25/01		UNLESS NOTED				
B	V11476	LEW	10/01/01	angles		projection	title CA, FC2-FC2A, 3mm, SM-8.3		
				dr	J. KILE	5/25/01			
				enrg	G. WARNER	5/25/01	product family FIBER OPTICS		
				chr	G. WARNER	5/25/01			
				appd	G. WARNER	5/25/01	size dwg no A4 57663		
sheet index	revision	B							
	sheet	1					scale 1:1		
							cage code 22526		

ACAD

PDM: Rev:B

STATUS:Released

Printed: Apr 08, 2008

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

FCI:

[57663-M001](#)