

Pelican MityLite 1900

www.pelicanproducts.us



Submersible

MityLite™ 1900 Flashlight

Unlike conventional flashlights that have a yellowish beam, the MityLite 1900 flashlight uses a hi-intensity Xenon lamp that produces a powerful, bright beam. Use this compact flashlight to cut through thick smoke, fog, and dust. It is submersible and comes with a twist-on shroud. The 1900 is ideal for any situation. Powered by 2 AAA alkaline cells.

Minimum Pack 6 ea.

Packaged Weight: 2.4 oz.

MityLite™ 1900 Flashlight Specifications

	High	
LIGHT SOURCE	Xenon	
BATTERIES	2 AAAA alkaline (Included)	
CHARGE TIME	N/A	
VOLTAGE	3	
LENGTH	4.09" (10.4 cm)	
WEIGHT w/ BATTERIES	1.6 oz. (0.05 kg)	
WEIGHT w/o BATTERIES	0.75 oz. (0.02 kg)	

	FL1 STANDARD	High	
LIGHT OUTPUT		11 LUMENS	
RUNTIME (hours/min)		1h 30m	
BEAM DISTANCE (meters)		45m	
PEAK BEAM INTENSITY (candela)		571cd	
WATERPROOF & SUBMERSIBLE		1m	

MityLite™ 1900 Flashlight Configurations

Cat. #	Description
1900	MityLite™ 1900 Flashlight (Carded)
1900T	MityLite™ 1900 Flashlight (Clear Gift Tube)
1900M	MityLite™ 1900 Flashlight Merchandiser Display

NSN List

NSN #	Description
6230-01-365-7647	1900T Orange
6230-01-463-8505	1900C
6230-01-522-3357	1900C Yellow
6230-01-281-3774	1900LM
6230-01-345-6314	1900T Black
6230-01-324-2950	1900T Orange
6230-01-518-2061	1900TNVG Black
6240-01-428-9410	1904 Lamp Module

MityLite™ 1900 Flashlight Accessories

Cat. #	Description
722	Helmet Light Holder
1904	MityLite™ 1900 Lamp Module

MityLite™ 1900 Flashlight Approvals



Class I, Div. 2; Gp ABCD, T3C; Class II; Div. 2; Gp G.



Ex ib e IIC T4 IP67 IEC Ex TSA06.0021X



Class I, Div. 1, GP C,D, T3C CONFORMS TO STD UL 783