

YAE14N4BOX

BURNDY® PRODUCTS

YAE14N4BOX

YAE14N4BOX : 16-14 NYLON RING 3/8 STU



ACTIVE

RoHS
compatible[Assistant](#)[Add to Favorites](#)[Email Datasheet](#) [Print Datasheet](#)

FCI Brings You More

[Contact our sales/technical support](#)[Sample request](#)[Price request](#)

Specifications

[Download document](#)**Dimensional Physical Approvals / Certifications Other Features****Dimensional**

Stud Hole (Size)	3/8 in.
Tongue Width (in)	0.53 in.
Wire Insulation Grip	Yes
Insulation Diameter (Max)	0.156 in.

Physical

Conductor Size	14 AWG 16 AWG
Element A Index	Hand Tools
Insulation Type	Nylon
Color Code	Blue
Conductor Size (Range)	16 AWG to 14 AWG

Approvals / Certifications

Military Listed	Yes
UL Listed	Yes
CSA Certified	Yes

Other Features

Tape Mounted Catalog Number	YAE18N4M
Tongue Type	Ring
Bulk Catalog Number	YAE18N4
UPC	78181056340
Keyword	smterm