

main menue



home
test & measurement
products
skills
download

online catalogue T&M

clamp-type test probes
▶ 0,64 mm system
▶ 2 mm system
▶ 2 mm Sicherheitssystem
▶ 4 mm system
▶ 4 mm sliding sleeve system
▶ 4 mm safety system
crocodile clips
test probes
oscilloscope test probes
measuring leads
plugs
sockets
sets
miscellaneous

company

portrait
corporate association
location maps
fairs and exhibitions
jobs
imprint
terms and conditions

Home ▶ clamp-type test probes ▶ clamp-type test probe ▶ KLEPS 2800

KLEPS 2800

datasheet for KLEPS 2800
article number: 972308101



[View Full-Size Image](#)



search online catalogue

Search

Messetermine

SPS/IPC/DRIVES
24. 11. 2015 - 26. 11. 2015

QR-Code



product description:	order number: 972 308-101
description:	Safety clamp-type test probe with insulated wide opening grip claws for contacting large measuring areas and leads with large cross-sections. 4 mm brass socket connection. Connects with safety measuring leads.
typ:	KLEPS 2800 rot/red
system:	4 mm safety system
order number:	972 308-101
clamping range:	10 mm
clamping typ:	grip claws
color	
other color versions:	
technical data	
measurement category acc. to IEC 61010:	CAT III
type of termination:	4 mm socket (unsprung)
rated voltage:	AC/DC 1000 V
rated current:	20 A
Please consider derating curve!	
contact resistance:	10 mOhm
material	
contact material:	grip claws: stainless steel socket: brass
contact surface material:	nickel
housing material:	PBT
environmental conditions:	
temperature range:	-25 °C to +80 °C
inflammable class:	
housing (basic material):	UL 94 HB
drawing	
	