



Search Results

Evaluate

- FAQ's

How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click to remove) Search Tips

Text Search: 'F9PE10L-NM2'

Your search criteria matched only one product, shown below

F9PE10L-NM2



- Pass all TIA/EIA-568-B.3 performance requirements
- 100% factory inspected end face geometry in compliance with Telcordia GR-326-CORE, Issue 3
- Typical insertion loss per connection: 0.25dB
- UPC polished (55dB minimum return loss)
- Include color-specific keys with positive and negative keying features to visually and mechanically distinguish connections to prevent unauthorized mating with unlike keyed or non-keyed adapters
- Part of a complete keyed LC system that includes *Opti-Core*® Patch Cords and Pigtails, *OptiCam*® Pre-Polished Cam Connectors, *Opticom*® Fiber Adapter Panels (FAPs) and *Mini-Com*® Adapter Modules
- Factory terminated and 100% tested for insertion loss and return loss
- Insertion loss and return loss data recorded for every singlemode patch cord
- Lifetime traceability of test data to a Q.C. number on each patch cord

- Highest quality flame retardant fiber optic cable with tight-buffered coating on each optical fiber

Additional lengths and availability: Keyed LC patch cords and pigtails are available in 1m – 10m lengths in 1m increments, and 15m, 20m, and 30m lengths. For other lengths, contact Customer Service for actual lead times.

Additional keyed colors include the following: G– Violet, H– Aqua, J– Rose, K– Slate, L– Brown, P– White, Q– Charcoal, R– Lavender, S– Peach, T– Steel Blue, V– Maroon and W– Mint.

• Part Number	F9PE10L-NM2
• RoHS Compliancy Status	Compliant
• Note	Intended for use in fixed installations which are outside the scope of RoHS.
• Part Description	LC (keyed L – Brown) to pigtail singlemode duplex pigtail, 1.6mm jacketed cable (one duplex keyed LC connector on one end and open on the other end) – 9/125µm.
• Product Type	Keyed LC Patch Cords
• Length (m)	2
• Fiber Compatibility	9/125µm
• Fiber Cable Size	1.6mm
• Fiber Cable Type	Jacketed
• Fiber Type	Singlemode
• Connector 1 Type	LC Connector - Keyed L - Brown
• Connector 2 Type	Pigtail
• Flammability Rating	Plenum (OFNP)
• Key Type and Color	Keyed L-Brown
• Pricing Description	LC (keyed L - Brown) to pigtail 9/125µm singlemode, duplex patch cord, 1.6mm jacketed cable, 2M
• Min. Order UOM	PC
• Min. Order Qty.	1
• BOM Qty. (# of Pkgs.)	0
• Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.