



13			12		11		10		9		8		7		6		5		4		3		2		1															
J	PACKAGING SEE NOTE 4 SHT 1		4-6 CKT		BULK		TAPE-N-REEL W/ VAC CAPS		N/A		BULK		TAPE-N-REEL W/ VAC CAPS		N/A		BULK		TAPE-N-REEL W/ VAC CAPS		N/A		BULK		BULK															
			8-100 CKT		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES W/ VAC CAPS		TUBES		TUBES															
	DIM. M±0.25 MM				6.10 (.240)				6.10 (.240)				6.10 (.240)				6.10 (.240)								8.13 (.320)		8.13 (.320)													
	PLATING				150 TIN				15 GOLD				30 GOLD												15 GOLD		30 GOLD													
	DIM. H				2.54 (.100)				2.54 (.100)				2.54 (.100)												4.57 (.180)		4.57 (.180)													
I	CKTS	DIM. A		DIM. B		EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	CKTS													
		MM	IN	MM	IN																																			
H	04	5.08	.200	2.54	.100	015-91-2040	015-91-6040	N/A	015-91-0040	015-91-6042	N/A	015-91-3040	015-91-6043	N/A		015-91-0048	015-91-5049	04	H																					
	06	7.62	.300	5.08	.200	015-91-2060	015-91-6060	N/A	015-91-0060	015-91-6062	N/A	015-91-3060	015-91-6063	N/A		015-91-0068	015-91-5069	06																						
	08	10.16	.400	7.62	.300	015-91-2080	015-91-6080	015-91-3087	015-91-0080	015-91-6082	015-91-3086	015-91-3080	015-91-6083	015-91-3088		015-91-0088	015-91-5089	08																						
	10	12.70	.500	10.16	.400	015-91-2100	015-91-6100	015-91-3107	015-91-0100	015-91-6102	015-91-3106	015-91-3100	015-91-6103	015-91-3108		015-91-0108	015-91-5109	10																						
H	12	15.24	.600	12.70	.500	015-91-2120	015-91-6120	015-91-3127	015-91-0120	015-91-6122	015-91-3126	015-91-3120	015-91-6123	015-91-3128		015-91-0128	015-91-5129	12	H																					
	14	17.78	.700	15.24	.600	015-91-2140	015-91-6140	015-91-3147	015-91-0140	015-91-6142	015-91-3146	015-91-3140	015-91-6143	015-91-3148		015-91-0148	015-91-5149	14																						
	16	20.32	.800	17.78	.700	015-91-2160	015-91-6160	015-91-3167	015-91-0160	015-91-6162	015-91-3166	015-91-3160	015-91-6163	015-91-3168		015-91-0168	015-91-5169	16																						
	18	22.86	.900	20.32	.800	015-91-2180		015-91-3187	015-91-0180		015-91-3186	015-91-3180		015-91-3188		015-91-0188	015-91-5189	18																						
G	20	25.40	1.000	22.86	.900	015-91-2200	015-91-6200	015-91-3207	015-91-0200	015-91-6202	015-91-3206	015-91-3200	015-91-6203	015-91-3208		015-91-0208	015-91-5209	20	G																					
	22	27.94	1.100	25.40	1.000	015-91-2220		015-91-3227	015-91-0220		015-91-3226	015-91-3220		015-91-3228		015-91-0228	015-91-5229	22																						
	24	30.48	1.200	27.94	1.100	015-91-2240		015-91-3247	015-91-0240		015-91-3246	015-91-3240		015-91-3248		015-91-0248	015-91-5249	24																						
	26	33.02	1.300	30.48	1.200	015-91-2260	015-91-6260	015-91-3267	015-91-0260	015-91-6262	015-91-3266	015-91-3260		015-91-3268		015-91-0268	015-91-5269	26																						
G	28	35.56	1.400	33.02	1.300	015-91-2280		015-91-3287	015-91-0280		015-91-3286	015-91-3280		015-91-3288		015-91-0288	015-91-5289	28	G																					
	30	38.10	1.500	35.56	1.400	015-91-2300		015-91-3307	015-91-0300		015-91-3306	015-91-3300		015-91-3308		015-91-0308	015-91-5309	30																						
	32	40.64	1.600	38.10	1.500	015-91-2320		015-91-3327	015-91-0320		015-91-3326	015-91-3320		015-91-3328		015-91-0328	015-91-5329	32																						
	34	43.18	1.700	40.64	1.600	015-91-2340		015-91-3347	015-91-0340		015-91-3346	015-91-3340		015-91-3348		015-91-0348	015-91-5349	34																						
F	36	45.72	1.800	43.18	1.700	015-91-2360		015-91-3367	015-91-0360		015-91-3366	015-91-3360		015-91-3368		015-91-0368	015-91-5369	36	F																					
	38	48.26	1.900	45.72	1.800	015-91-2380		015-91-3387	015-91-0380		015-91-3386	015-91-3380		015-91-3388		015-91-0388	015-91-5389	38																						
	40	50.80	2.000	48.26	1.900	015-91-2400	015-91-6400	015-91-3407	015-91-0400	015-91-6402	015-91-3406	015-91-3400	015-91-6403	015-91-3408		015-91-0408	015-91-5409	40																						
	42	53.34	2.100	50.80	2.000	015-91-2420		015-91-3427	015-91-0420		015-91-3426	015-91-3420		015-91-3428		015-91-0428	015-91-5429	42																						
F	44	55.88	2.200	53.34	2.100	015-91-2440		015-91-3447	015-91-0440		015-91-3446	015-91-3440		015-91-3448		015-91-0448	015-91-5449	44	F																					
	46	58.42	2.300	55.88	2.200	015-91-2460		015-91-3467	015-91-0460		015-91-3466	015-91-3460		015-91-3468		015-91-0468	015-91-5469	46																						
	48	60.96	2.400	58.42	2.300	015-91-2480		015-91-3487	015-91-0480		015-91-3486	015-91-3480		015-91-3488		015-91-0488	015-91-5489	48																						
	50	63.50	2.500	60.96	2.400	015-91-2500	015-91-6500	015-91-3507	015-91-0500	015-91-6502	015-91-3506	015-91-3500	015-91-6503	015-91-3508		015-91-0508	015-91-5509	50																						
E	52	66.04	2.600	63.50	2.500	015-91-2520		015-91-3527	015-91-0520		015-91-3526	015-91-3520		015-91-3528		015-91-0528	015-91-5529	52	E																					
	54	68.58	2.700	66.04	2.600	015-91-2540		015-91-3547	015-91-0540		015-91-3546	015-91-3540		015-91-3548		015-91-0548	015-91-5549	54																						
	56	71.12	2.800	68.58	2.700	015-91-2560		015-91-3567	015-91-0560		015-91-3566	015-91-3560		015-91-3568		015-91-0568	015-91-5569	56																						
	58	73.66	2.900	71.12	2.800	015-91-2580		015-91-3587	015-91-0580		015-91-3586	015-91-3580		015-91-3588		015-91-0588	015-91-5589	58																						
E	60	76.20	3.000	73.66	2.900	015-91-2600		015-91-3607	015-91-0600		015-91-3606	015-91-3600		015-91-3608		015-91-0608	015-91-5609	60	E																					
	62	78.74	3.100	76.20	3.000	015-91-2620																																		

13		12		11				10		8		7		6		5		4		3		2		1	
J		IN TAPE AND REEL WITH SHALLOW POCKET TAPE												BULK / IN TUBES										J	
		PACKAGING SEE NOTE 4. SHT 1		4-8 CKT		TAPE-N-REEL W/ VAC CAPS		TAPE-N-REEL W/ VAC CAPS										BULK		BULK					
				10-100 CKT		TAPE-N-REEL W/ VAC CAPS		TAPE-N-REEL W/ VAC CAPS										TUBES		TUBES					
		DIM. M±0.25 MM				6.10 (.240)		6.10 (.240)										8.13 (.320)		13.59 (.535)					
		PLATING				30 GOLD		15 GOLD										150 TIN		150 TIN					
		DIM. H				2.54 (.100)		2.54 (.100)										4.57 (.180)		4.57 (.180)					
I		CKTS		DIM. A		DIM. B		EDP NUMBER		EDP NUMBER								EDP NUMBER		EDP NUMBER		CKTS			
				MM	IN	MM	IN																		
		04	5.08	.200	2.54	.100																			
		06	7.62	.300	5.08	.200			015-91-6068																
		08	10.16	.400	7.62	.300			015-91-6088																
		10	12.70	.500	10.16	.400			015-91-6108								713088010		71308-8210		10				
		12	15.24	.600	12.70	.500																			
		14	17.78	.700	15.24	.600	015-91-6148																		
		16	20.32	.800	17.78	.700											713088016								
		18	22.86	.900	20.32	.800																			
		20	25.40	1.000	22.86	.900																			
		22	27.94	1.100	25.40	1.000																			
		24	30.48	1.200	27.94	1.100																			
		26	33.02	1.300	30.48	1.200																			
		28	35.56	1.400	33.02	1.300																			
		30	38.10	1.500	35.56	1.400																			
		32	40.64	1.600	38.10	1.500																			
		34	43.18	1.700	40.64	1.600																			
		36	45.72	1.800	43.18	1.700																			
		38	48.26	1.900	45.72	1.800																			
		40	50.80	2.000	48.26	1.900																			
		42	53.34	2.100	50.80	2.000																			
		44	55.88	2.200	53.34	2.100																			
		46	58.42	2.300	55.88	2.200																			
		48	60.96	2.400	58.42	2.300																			
		50	63.50	2.500	60.96	2.400																			
		52	66.04	2.600	63.50	2.500																			
		54	68.58	2.700	66.04	2.600																			
		56	71.12	2.800	68.58	2.700																			
		58	73.66	2.900	71.12	2.800																			
		60	76.20	3.000	73.66	2.900																			
		62	78.74	3.100	76.20	3.000																			
		64	81.28	3.200	78.74	3.100																			
		66	83.82	3.300	81.28	3.200																			
		68	86.36	3.400	83.82	3.300																			
		70	88.90	3.500	86.36	3.400																			
		72	91.44	3.600	88.90	3.500																			
		74	93.98	3.700	91.44	3.600																			
		76	96.52	3.800	93.98	3.700																			
		78	99.06	3.900	96.52	3.800																			
		80	101.60	4.000	99.06	3.900																			
		82	104.14	4.100	101.60	4.000																			
		84	106.68	4.200	104.14	4.100																			
		86	109.22	4.300	106.68	4.200																			
		88	111.76	4.400	109.22	4.300																			
		90	114.30	4.500	111.76	4.400																			
		92	116.84	4.600	114.30	4.500																			
		94	119.38	4.700	116.84	4.600																			
		96	121.92	4.800	119.38	4.700																			
		98	124.46	4.900	121.92	4.800																			
		100	127.00	5.000	124.46	4.900																			
B		NO PEG VERSION										SEE SHEET 1 EC NO: UCP2014-0809 DRAWN:KIPPER 2013/08/20 CHKD:JBELL 2013/08/20 APPR:FSMITH 2013/09/03		QUALITY SYMBOLS ▽=0 ▽=0 ▽=0		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE		DESIGN UNITS INCH		THIRD ANGLE PROJECTION	
																mm		INCH		DRAWN BY KMS		DATE 1999/10/15			
A		(ALSO SEE SHEET 2)										K5		REV		ANGULAR ±1/2° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE C		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		DOCUMENT NO. SD-71308-001		SHEET NO. 3 OF 6	
1b_frame_C_P_AM.T Rev. G 2012/01/11		12		11		10		9		8		7		6		5		4		3		2		1	

13		12		11		10		9		8		7		6		5		4		3		2		1			
J		PACKAGING SEE NOTE 4 SHT 1				4-8 CKT		BULK		TAPE-N-REEL W/ VAC CAPS		BULK		TAPE-N-REEL W/ VAC CAPS		BULK		TAPE-N-REEL W/ VAC CAPS		BULK		BULK		BULK			
						10-100 CKT		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES		TUBES		TUBES			
						DIM. M±0.25 MM		6.10 (.240)		6.10 (.240)		6.10 (.240)		6.10 (.240)		8.13 (.320)		8.13 (.320)		8.13 (.320)							
						PLATING		150 TIN		15 GOLD		30 GOLD		150 TIN		15 GOLD		30 GOLD									
						DIM. H		2.54 (.100)		2.54 (.100)		2.54 (.100)		4.57 (.180)		4.57 (.180)		4.57 (.180)									
I	CKTS	DIM. A		DIM. B		DIM. C		EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	CKTS			
		MM	IN	MM	IN	MM	IN																				
04	5.08	.200	2.54	.100	----	----	015-91-1041	015-91-6044	015-91-1042	015-91-6045	015-91-1043	015-91-6046	015-91-1044	015-91-0047	015-91-1040									04			
06	7.62	.300	5.08	.200	2.54	.100	015-91-1061	015-91-6064	015-91-1062	015-91-6065	015-91-1063	015-91-6066	015-91-1064	015-91-0067	015-91-1060									06			
08	10.16	.400	7.62	.300	5.08	.200	015-91-1081	015-91-6084	015-91-1082	015-91-6085	015-91-1083	015-91-6086	015-91-1084	015-91-0087	015-91-1080									08			
10	12.70	.500	10.16	.400	7.62	.300	015-91-1101	015-91-6104	015-91-1102	015-91-6105	015-91-1103	015-91-6106	015-91-1104	015-91-0107	015-91-1100									10			
12	15.24	.600	12.70	.500	10.16	.400	015-91-1121		015-91-1122		015-91-1123		015-91-1124	015-91-0127	015-91-1120									12			
14	17.78	.700	15.24	.600	12.70	.500	015-91-1141	015-91-6144	015-91-1142	015-91-6145	015-91-1143	015-91-6146	015-91-1144	015-91-0147	015-91-1140									14			
16	20.32	.800	17.78	.700	15.24	.600	015-91-1161	015-91-6164	015-91-1162	015-91-6165	015-91-1163	015-91-6166	015-91-1164	015-91-0167	015-91-1160									16			
18	22.86	.900	20.32	.800	17.78	.700	015-91-1181		015-91-1182		015-91-1183		015-91-1184	015-91-0187	015-91-1180									18			
20	25.40	1.000	22.86	.900	20.32	.800	015-91-1201		015-91-1202		015-91-1203		015-91-1204	015-91-0207	015-91-1200									20			
22	27.94	1.100	25.40	1.000	22.86	.900	015-91-1221		015-91-1222		015-91-1223		015-91-1224	015-91-0227	015-91-1220									22			
24	30.48	1.200	27.94	1.100	25.40	1.000	015-91-1241	71308-6901	015-91-1242		015-91-1243		015-91-1244	015-91-0247	015-91-1240									24			
26	33.02	1.300	30.48	1.200	27.94	1.100	015-91-1261		015-91-1262		015-91-1263		015-91-1264	015-91-0267	015-91-1260									26			
28	35.56	1.400	33.02	1.300	30.48	1.200	015-91-1281		015-91-1282		015-91-1283		015-91-1284	015-91-0287	015-91-1280									28			
30	38.10	1.500	35.56	1.400	33.02	1.300	015-91-1301		015-91-1302		015-91-1303		015-91-1304	015-91-0307	015-91-1300									30			
32	40.64	1.600	38.10	1.500	35.56	1.400	015-91-1321		015-91-1322		015-91-1323		015-91-1324	015-91-0327	015-91-1320									32			
34	43.18	1.700	40.64	1.600	38.10	1.500	015-91-1341		015-91-1342		015-91-1343		015-91-1344	015-91-0347	015-91-1340									34			
36	45.72	1.800	43.18	1.700	40.64	1.600	015-91-1361		015-91-1362		015-91-1363		015-91-1364	015-91-0367	015-91-1360									36			
38	48.26	1.900	45.72	1.800	43.18	1.700	015-91-1381		015-91-1382		015-91-1383		015-91-1384	015-91-0387	015-91-1380									38			
40	50.80	2.000	48.26	1.900	45.72	1.800	015-91-1401		015-91-1402		015-91-1403		015-91-1404	015-91-0407	015-91-1400									40			
42	53.34	2.100	50.80	2.000	48.26	1.900	015-91-1421		015-91-1422		015-91-1423		015-91-1424	015-91-0427	015-91-1420									42			
44	55.88	2.200	53.34	2.100	50.80	2.000	015-91-1441		015-91-1442		015-91-1443		015-91-1444	015-91-0447	015-91-1440									44			
46	58.42	2.300	55.88	2.200	53.34	2.100	015-91-1461		015-91-1462		015-91-1463		015-91-1464	015-91-0467	015-91-1460									46			
48	60.96	2.400	58.42	2.300	55.88	2.200	015-91-1481		015-91-1482		015-91-1483		015-91-1484	015-91-0487	015-91-1480									48			
50	63.50	2.500	60.96	2.400	58.42	2.300	015-91-1501	015-91-6504	015-91-1502	015-91-6505	015-91-1503	015-91-6506	015-91-1504	015-91-0507	015-91-1500									50			
52	66.04	2.600	63.50	2.500	60.96	2.400	015-91-1521		015-91-1522		015-91-1523	71308-5203	015-91-1524	015-91-0527	015-91-1520									52			
54	68.58	2.700	66.04	2.600	63.50	2.500	015-91-1541		015-91-1542		015-91-1543		015-91-1544	015-91-0547	015-91-1540									54			
56	71.12	2.800	68.58	2.700	66.04	2.600	015-91-1561		015-91-1562		015-91-1563		015-91-1564	015-91-0567	015-91-1560									56			
58	73.66	2.900	71.12	2.800	68.58	2.700	015-91-1581		015-91-1582		015-91-1583		015-91-1584	015-91-0587	015-91-1580									58			
60	76.20	3.000	73.66	2.900	71.12	2.800	015-91-1601		015-91-1602		015-91-1603		015-91-1604	015-91-0607	015-91-1600									60			
62	78.74	3.100	76.20	3.000	73.66	2.900	015-91-1621		015-91-1622		015-91-1623		015-91-1624	015-91-0627	015-91-1620									62			
64	81.28	3.200	78.74	3.100	76.20	3.000	015-91-1641		015-91-1642		015-91-1643		015-91-1644	015-91-0647	015-91-1640									64			
66	83.82	3.300	81.28	3.200	78.74	3.100	015-91-1661		015-91-1662		015-91-1663		015-91-1664	015-91-0667	015-91-1660									66			
68	86.36	3.400	83.82	3.300	81.28	3.200	015-91-1681		015-91-1682		015-91-1683		015-91-1684	015-91-0687	015-91-1680									68			
70	88.90	3.500	86.36	3.400	83.82	3.300	015-91-1701		015-91-1702		015-91-1703		015-91-1704	015-91-0707	015-91-1700									70			
72	91.44	3.600	88.90	3.500	86.36	3.400	015-91-1721		015-91-1722		015-91-1723		015-91-1724	015-91-0727	015-91-1720									72			
74	93.98	3.700	91.44	3.600	88.90	3.500	015-91-1741		015-91-1742		015-91-1743		015-91-1744	015-91-0747	015-91-1740									74			
76	96.52	3.800	93.98	3.700	91.44	3.600	015-91-1761		015-91-1762		015-91-1763		015-91-1764	015-91-0767	015-91-1760									76			
78	99.06	3.900	96.52	3.800	93.98	3.700	015-91-1781		015-91-1782		015-91-1783		015-91-1784	015-91-0787	015-91-1780									78			
80	101.60	4.000	99.06	3.900	96.52	3.800	015-91-1801		015-91-1802		015-91-1803		015-91-1804	015-91-0807	015-91-1800									80			
82	104.14	4.100	101.60	4.000	99.06	3.900	71308-4082		71308-4182		71308-4282		71308-5082	71308-5182	71308-5282									82			
84	106.68	4.200	104.14	4.100	101.60	4.000	71308-4084		71308-4184		71308-4284		71308-5084	71308-5184	71308-5284									84			
86	109.22	4.300	106.68	4.200	104.14	4.100	71308-4086		71308-4186		71308-4286		71308-5086	71308-5186	71308-5286									86			
88	111.76	4.400	109.22	4.300	106.68	4.200	71308-4088		71308-4188		71308-4288		71308-5088	71308-5188	71308-5288									88			
90	114.30	4.500	111.76	4.400	109.22																						

[illegible]

		13		12		11		10		9		8		7		6		5		4		3		2		1																											
J		PEG OPTION																										J																									
		NO PEG VERSION														NO PEG VERSION				LONG PEG VERSION (.130")				SHORT PEG VERSION (.055")																													
		PACKAGING SEE NOTE 4, SHT 1		4-6 CKT		BULK		TAPE-N-REEL W/VAC CAPS		N/A		4-8 CKT		TAPE-N-REEL W/VAC CAPS		BULK		BULK		BULK		TAPE-N-REEL W/VAC CAPS		BULK		BULK				TAPE-N-REEL W/ VAC CAPS																							
				8-100 CKT		TUBES		TAPE-N-REEL W/VAC CAPS		TUBES W/ VAC CAPS				10-100 CKT		TAPE-N-REEL W/VAC CAPS		TUBES		TUBES		TUBES		TAPE-N-REEL W/VAC CAPS		TUBES				BULK		TAPE-N-REEL W/ VAC CAPS																					
		DIM. M±0.25 MM										6.10 (.240)										8.13(.320)										6.10 (.240)																					
		PLATING										59 TIN										59 TIN										59 TIN										59 TIN											
		DIM. H										2.54(.100)										4.57(.180)										4.57(.180)										2.54(.100)											
I		CKTS		DIM. A		DIM. B		DIM. C		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		CKTS																							
				MM	IN	MM	IN	MM	IN																																												
		04		5.08 .200		2.54 .100		---		---		71308-5404		71308-5504		N/A						71308-6404		71308-6504		71308-6604				04																							
		06		7.62 .300		5.08 .200		2.54 .100		---		71308-5406		71308-5506		N/A						71308-6406		71308-6506		71308-6606		71308-6706		71308-6806																							
		08		10.16 .400		7.62 .300		5.08 .200		---		71308-5408		71308-5508		71308-5608						71308-6408		71308-6508		71308-6608		71308-6708		71308-6808																							
H		10		12.70 .500		10.16 .400		7.62 .300		---		71308-5410		71308-5510		71308-5610				71308-5810		71308-5910		71308-6410		71308-6510		71308-6610		71308-6810																							
		12		15.24 .600		12.70 .500		10.16 .400		---		71308-5412		71308-5512		71308-5612								71308-6412				71308-6612																									
		14		17.78 .700		15.24 .600		12.70 .500		---		71308-5414		71308-5514		71308-5614								71308-6414		71308-6514		71308-6614																									
		16		20.32 .800		17.78 .700		15.24 .600		---		71308-5416		71308-5516		71308-5616				71308-5816				71308-6416		71308-6516		71308-6616																									
		18		22.86 .900		20.32 .800		17.78 .700		---		71308-5418				71308-5618								71308-6418				71308-6618																									
		20		25.40 1.000		22.86 .900		20.32 .800		---		71308-5420		71308-5520		71308-5620								71308-6420				71308-6620																									
		22		27.94 1.100		25.40 1.000		22.86 .900		---		71308-5422				71308-5622								71308-6422				71308-6622																									
		24		30.48 1.200		27.94 1.100		25.40 1.000		---		71308-5424				71308-5624				71308-5724		71308-5824		71308-6424				71308-6624																									
G		26		33.02 1.300		30.48 1.200		27.94 1.100		---		71308-5426				71308-5626								71308-6426				71308-6626		71308-6726																							
		28		35.56 1.400		33.02 1.300		30.48 1.200		---		71308-5428				71308-5628								71308-6428				71308-6628																									
		30		38.10 1.500		35.56 1.400		33.02 1.300		---		71308-5430				71308-5630								71308-6430				71308-6630																									
		32		40.64 1.600		38.10 1.500		35.56 1.400		---		71308-5432				71308-5632								71308-6432				71308-6632																									
		34		43.18 1.700		40.64 1.600		38.10 1.500		---		71308-5434				71308-5634								71308-6434				71308-6634																									
		36		45.72 1.800		43.18 1.700		40.64 1.600		---		71308-5436				71308-5636								71308-6436				71308-6636																									
		38		48.26 1.900		45.72 1.800		43.18 1.700		---		71308-5438				71308-5638								71308-6438				71308-6638																									
F		40		50.80 2.000		48.26 1.900		45.72 1.800		---		71308-5440		71308-5540		71308-5640								71308-6440				71308-6640																									
		42		53.34 2.100		50.80 2.000		48.26 1.900		---		71308-5442				71308-5642								71308-6442				71308-6642																									
		44		55.88 2.200		53.34 2.100		50.80 2.000		---		71308-5444				71308-5644								71308-6444				71308-6644																									
		46		58.42 2.300		55.88 2.200		53.34 2.100		---		71308-5446				71308-5646								71308-6446				71308-6646																									
		48		60.96 2.400		58.42 2.300		55.88 2.200		---		71308-5448				71308-5648								71308-6448				71308-6648																									
		50		63.50 2.500		60.96 2.400		58.42 2.300		---		71308-5450		71308-5550		71308-5650								71308-6450		71308-6550		71308-6650																									
		52		66.04 2.600		63.50 2.500		60.96 2.400		---		71308-5452				71308-5652								71308-6452				71308-6652																									
E		54		68.58 2.700		66.04 2.600		63.50 2.500		---		71308-5454				71308-5654								71308-6454				71308-6654																									
		56		71.12 2.800		68.58 2.700		66.04 2.600		---		71308-5456				71308-5656								71308-6456				71308-6656																									
		58		73.66 2.900		71.12 2.800		68.58 2.700		---		71308-5458				71308-5658								71308-6458				71308-6658																									
		60		76.20 3.000		73.66 2.900		71.12 2.800		---		71308-5460				71308-5660								71308-6460				71308-6660																									
		62		78.74 3.100		76.20 3.000		73.66 2.900		---		71308-5462				71308-5662								71308-6462				71308-6662																									
		64		81.28 3.200		78.74 3.100		76.20 3.000		---		71308-5464				71308-5664								71308-6464				71308-6664																									
		66		83.82 3.300		81.28 3.200		78.74 3.100		---		71308-5466				71308-5666								71308-6466				71308-6666																									
D		68		86.36 3.400		83.82 3.300		81.28 3.200		---		71308-5468				71308-5668								71308-6468				71308-6668																									
		70		88.90 3.500		86.36 3.400		83.82 3.300		---		71308-5470				71308-5670								71308-6470				71308-6670																									
		72		91.44 3.600		88.90 3.500		86.36 3.400		---		71308-5472				71308-5672								71308-6472				71308-6672																									
		74		93.98 3.700		91.44 3.600		88.90 3.500		---		71308-5474				71308-5674								71308-6474				71308-6674																									
		76		96.52 3.800		93.98 3.700		91.44 3.600		---		71308-5476				71308-5676								71308-6476				71308-6676																									
		78		99.06 3.900		96.52 3.800		93.98 3.700		---		71308-5478				71308-5678								71308-6478				71308-6678																									
		80		101.60 4.000		99.06 3.900		96.52 3.800		---		71308-5480				71308-5680								71308-6480				71308-6680																									
C		82		104.14 4.100		101.60 4.000		99.06 3.900		---		71308-5482				71308-5682								71308-6482				71308-6682																									
		84		106.68 4.200		104.14 4.100		101.60 4.000		---		71308-5484				71308-5684								71308-6484				71308-6684																									
		86		109.22 4.300		106.68 4.200		104.14 4.100		---		71308-5486				71308-5686								71308-6486				71308-6686																									
		88		111.76 4.400		109.22 4.300		106.68 4.200		---		71308-5488				71308-5688								71308-6488				71308-6688																									
		90		114.30 4.500		111.76 4.400		109.22 4.300		---		71308-5490				71308-5690								71308-6490				71308-6690																									
		92		116.84 4.600		114.30 4.500		111.76 4.400		---		71308-5492				71308-5692								71308-6492				71308-6692																									
		94		119.38 4.700		116.84 4.600		114.30 4.500		---		71308-5494				71308-5694								71308-6494				71308-6694																									
		96		121.92 4.800		119.38 4.700		116.84 4.600		---		71308-5496				71308-5696								71308-6496				71308-6696																									
		98		124.46 4.900		121.92 4.800		119.38 4.700		---		71308-5498				71308-5698								71308-6498				71308-6698																									
		100		127.00 5.000		124.46 4.900		121.92 4.800		---		71308-5500				71308-5700								71308-6500				71308-6700																									
B		59 TIN PLATE ASSEMBLIES										SEE SHEET 1 EC NO: UCP2014-0809 DRWN:MKIPPER 2013/08/20 CHKD:JBELL 2013/08/20 APPR:FSMITH 2013/09/03		REV		QUALITY SYMBOLS ▽=0 ▽=0 ▽=0		GENERAL TOLERANCES (UNLESS SPECIFIED)				DIMENSION STYLE MM/IN				SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION																							
																		mm		INCH		DRAWN BY		DATE		TITLE		INCH																									
A																		4 PLACES ± --- ± ---		3 PLACES ± --- ± .005		2 PLACES ± 0.13 ± .010		1 PLACE ± 0.25 ± ---		0 PLACE ± --- ± ---		ANGULAR ±1/2°		MATERIAL NO. SEE TABLE		DOCUMENT NO. SD-71308-001		SHEET NO. 6 OF 6																			
																																				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE C		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
		1b_frame_C_P_AM_T Rev. G 2012/01/11		12		11		10		9		8		7		6		5		4		3		2		1																											

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

15-91-1808