

Tungsten Halogen

Lamps for spot/fog & headlights



Reference No	Volt	Watt	Type	Dim(mm)
H1				
465	6v	55w	H1	P14.5s
448	12v	55w	H1	P14.5s
448XB	12v	55w	H1 X/Blue	P14.5s
448XP	12v	55w	H1 X/+60%	P14.5s
481	12v	100w	H1	P14.5s
491	12v	130w	H1	P14.5s
461	24v	100w	H1	P14.5s
466	24v	70w	H1	P14.5s
• 466HD	24v	70w	H1	P14.5s




Fig 47

H2				
479	12v	55w	H2	X511
482	12v	100w	H2	X511
492	12v	130w	H2	X511
480	24v	70w	H2	X511
462	24v	100w	H2	X511




Fig 48

H3				
455	6v	55w	H3	PK22s
453	12v	55w	H3	PK22s
454	12v	35w	H3	PK22s
483	12v	100w	H3	PK22s
493	12v	130w	H3	PK22s
460	24v	70w	H3	PK22s
463	24v	100w	H3	PK22s
442	48v	45w	H3	PK22s




Fig 49

H4				
444	12v	35/35	HS1	Px43t-38
472	12v	60/55	H4	P43t
472A	12v	60/55	H4Amber	P43t
472S	12v	60/55	H4Seasons	P43t
472XB	12v	60/55	H4 X/Blue	P43t
472XP	12v	60/55	H4 X/+60%	P43t
484	12v	100/80	H4	P43t
494	12v	130/90	H4	P43t
473	12v	100/55	H4	P43t
475	24v	75/70	H4	P43t
475S	24v	75/70	H4 Seasons	P43t
475XB	24v	75/70	H4 X/Blue	P43t
• 475HD	24v	75/70	H4	P43t
496	24v	100/80	H4	P43t
* 140180	12v	60/35	H4	Alt.Lug
* 140339	12v	65/55	3Lug	BA20




Fig 50

• Heavy Duty

* Motorcycle Specials