

Overall Beldfoil® Shield

437 104


Belden

Description UL AWM Style	Trade No. UL NEC C(UL) CEC Type	No. of Pairs	Standard Lengths		Std. Unit Lbs. ea.	Nominal D.C.R.		Nominal O.D.		Nom. Imp. (ohms)	Nom. Vel. of Prop.	Nominal Capacitance			
			ft.	m		Cond.	Shield	Inch	mm			* pF/ ft.	* pF/ m	** pF/ ft.	** pF/ m

Stranded Conductors (7x32)

Product Description

Tinned copper, S-R PVC insulated, twisted pairs. Overall Beldfoil aluminum-polyester shield. 24 AWG stranded tinned copper drain wire. Chrome PVC jacket. Color code chart No. 3. Technical Information Section.

 Shorting Fold Beldfoil 100% Shield Coverage 2464 300V 80°C AWM I A See Attenuation, Rise Time and Bit Rate data for this series on page 91.	9501 NEC CMG CEC CMG	1	100 U-500 500 U-1000 1000	30.5 U-152.4 152.4 U-304.8 304.8	1.7 7.7 7.4 14.3 14.0	24Ω/M' 78.7Ω/km	18Ω/M' 59.1Ω/km	.156	3.96	75	60%	40	131	74	243	
	9502 NEC CMG CEC CMG P-MSHA- SC-7K- 182037	2	100 U-500 500 U-1000 1000 10000	30.5 U-152.4 152.4 U-304.8 304.8 3048.0	3.0 14.7 14.7 28.4 28.9 287.8	24Ω/M' 78.7Ω/km	17Ω/M' 55.8Ω/km	.222	5.64	75	60%	30	98	50	164	
									For Plenum version, see 82502.							
	9503 NEC CMG CEC CMG	3	100 U-500 500 U-1000 1000	30.5 U-152.4 152.4 U-304.8 304.8	3.3 14.7 15.3 28.7 29.6	24Ω/M' 78.7Ω/km	17Ω/M' 55.8Ω/km	.232	5.89	75	60%	30	98	50	164	
									For Plenum versions, see 89503.							
9504 NEC CMG CEC CMG	4	100 U-500 500 U-1000 1000	30.5 U-152.4 152.4 U-304.8 304.8	4.1 18.2 18.9 35.5 36.5	24Ω/M' 78.7Ω/km	17Ω/M' 55.8Ω/km	.265	6.73	75	60%	30	98	50	164		
								For Plenum versions, see 89504 or 82504.								
9505 NEC CMG CEC CMG	5	100 U-500 500 U-1000 1000	30.5 U-152.4 152.4 U-304.8 304.8	4.6 21.8 22.7 43.2 46.5	24Ω/M' 78.7Ω/km	17Ω/M' 55.8Ω/km	.289	7.34	75	60%	30	98	50	164		
								For Plenum versions, see 89505 or 82505.								

Paired
Overall Beldfoil® Shield

761175
761138




Computer Cables for EIA RS-232 Applications

Description UL AWM Style	Trade No. UL NEC C(UL) CEC Type	No. of Pairs	Standard Lengths		Std. Unit Lbs. ea.	Nominal D.C.R.		Nominal O.D.		Nom. Imp. (ohms)	Nom. Vel. of Prop.	Nominal Capacitance			
			ft.	m		Cond.	Shield	Inch	mm			* pF/ ft.	* pF/ m	** pF/ ft.	** pF/ m

24 Gage (cont'd.)
Stranded Conductors (7x32)
S-R PVC Insulated

Product Description

Tinned copper, S-R PVC insulated, twisted pairs. Overall Beldfoil aluminum-polyester shield. 24 AWG stranded tinned copper drain wire. Chrome PVC jacket. Color code chart No. 3, Technical Information Section.

 Beldfoil 100% Shield Coverage 2464 300V 80°C AWM I A See Attenuation, Rise Time and Bit Rate Data for this series on page 91.	9506 NEC CMG CEC CMG	6	100 U-500 500 U-1000 1000	30.5 U-152.4 152.4 U-304.8 304.8	5.2 24.3 25.2 47.6 52.0	24Ω/M' 78.7Ω/km	16Ω/M' 52.5Ω/km	.289	7.34	75	60%	30	98	50	164
	For Plenum version, see 82506.														
	9507 NEC CMG CEC CMG	7	100 U-500 500 U-1000 1000	30.5 U-152.4 152.4 U-304.8 304.8	5.8 25.8 26.6 51.1 54.4	24Ω/M' 78.7Ω/km	16.5Ω/M' 54.1Ω/km	.294	7.47	75	60%	30	98	50	164
	9508 NEC CMG CEC CMG	8	100 500 1000	30.5 152.4 304.8	6.6 30.4 62.0	24Ω/M' 78.7Ω/km	16.5Ω/M' 54.1Ω/km	.324	8.23	75	60%	30	98	50	164
	9509 NEC CMG CEC CMG	9	100 500 1000	30.5 152.4 304.8	7.3 33.4 68.8	24Ω/M' 78.7Ω/km	16.5Ω/M' 54.1Ω/km	.334	8.48	75	60%	30	98	50	164
	For Plenum version, see 82509.														
	9510 NEC CMG CEC CMG	10	100 500 1000	30.5 152.4 304.8	7.7 39.5 75.2	24Ω/M' 78.7Ω/km	16.5Ω/M' 54.1Ω/km	.368	9.34	75	60%	30	98	50	164
	9515 NEC CMG CEC CMG	15	100 500 1000	30.5 152.4 304.8	10.4 53.0 102.3	24Ω/M' 78.7Ω/km	16.5Ω/M' 54.1Ω/km	.417	10.6	75	60%	30	98	50	164
	9519 NEC CMG CEC CMG	19	100 500 1000	30.5 152.4 304.8	12.7 62.8 121.8	24Ω/M' 78.7Ω/km	16.5Ω/M' 54.1Ω/km	.448	11.4	75	60%	30	98	50	164
	9525 NEC CMG CEC CMG	25	100 500 1000	30.5 152.4 304.8	15.9 80.3 156.5	24Ω/M' 78.7Ω/km	16.5Ω/M' 54.1Ω/km	.503	12.8	75	60%	30	98	50	164
	9550 NEC CMG CEC CMG	50	100 500 ^{ns} 1000 ^{ns}	30.5 152.4 304.8	30.5 153.2 309.9	24Ω/M' 78.7Ω/km	15.2Ω/M' 49.9Ω/km	.708	18.0	75	60%	30	98	50	164
Color code: Request Technical Bulletin T/8-4.															

* Capacitance between conductors.

** Capacitance between one conductor and other conductors connected to shield.

^{ns} Spools are one piece, but length may vary -0 to +20% from length shown.

Color Code Chart No. 2 and 2R (ICEA—Insulated Cable Engineers Association)
Chart No. 1 Standard 2R—These cables feature a ring band striping. 2—These cables feature a spiral stripe.

Cond.	Color	Cond.	Color	Cond.	Color	Cond.	Color
1st	Black	1st	Black	14th	Green/White	27th	Blue/Black/White
2nd	White	2nd	White	15th	Blue/White	28th	Black/Red/Green
3rd	Red	3rd	Red	16th	Black/Red	29th	White/Red/Green
4th	Green	4th	Green	17th	White/Red	30th	Red/Black/Green
5th	Brown	5th	Orange	18th	Orange/Red	31st	Green/Black/Orange
6th	Blue	6th	Blue	19th	Blue/Red	32nd	Orange/Black/Green
7th	Orange	7th	White/Black	20th	Red/Green	33rd	Blue/White/Orange
8th	Yellow	8th	Red/Black	21st	Orange/Green	34th	Black/White/Orange
9th	Purple	9th	Green/Black	22nd	Black/White/Red	35th	White/Red/Orange
10th	Gray	10th	Orange/Black	23rd	White/Black/Red	36th	Orange/White/Blue
11th	Pink	11th	Blue/Black	24th	Red/Black/White	37th	White/Red/Blue
12th	Tan	12th	Black/White	25th	Green/Black/White	38th	Black/White/Green
		13th	Red/White	26th	Orange/Black/White	39th	White/Black/Green
18 Gage conductors in cables 8446 through 8449 are Black and White.							
						40th	Red/White/Green
						41st	Green/White/Blue
						42nd	Orange/Red/Green
						43rd	Blue/Red/Green
						44th	Black/White/Blue
						45th	White/Black/Blue
						46th	Red/White/Blue
						47th	Green/Orange/Red
						48th	Orange/Red/Blue
						49th	Blue/Orange/Red
						50th	Black/Orange/Red

Color Code Chart No. 3 for Paired Cables (Belden Standard)

Pair No.	Color Combination	Pair No.	Color Combination	Pair No.	Color Combination	Pair No.	Color Combination
1	Black & Red	11	Red & Yellow	21	White & Brown	31	Purple & White
2	Black & White	12	Red & Brown	22	White & Orange	32	Purple & Dark Green
3	Black & Green	13	Red & Orange	23	Blue & Yellow	33	Purple & Light Blue
4	Black & Blue	14	Green & White	24	Blue & Brown	34	Purple & Yellow
5	Black & Yellow	15	Green & Blue	25	Blue & Orange	35	Purple & Brown
6	Black & Brown	16	Green & Yellow	26	Brown & Yellow	36	Purple & Black
7	Black & Orange	17	Green & Brown	27	Brown & Orange	37	Gray & White
8	Red & White	18	Green & Orange	28	Orange & Yellow		
9	Red & Green	19	White & Blue	29	Purple & Orange		
10	Red & Blue	20	White & Yellow	30	Purple & Red		

Color Code Chart No. 4 for Paired Cables

Pair No.	Color Combination	Pair No.	Color Combination	Pair No.	Color Combination	Pair No.	Color Combination	Pair No.	Color Combination
1st	White & Blue	6th	Red & Blue	11th	Black & Blue	16th	Yellow & Blue	21st	Violet & Blue
2nd	White & Orange	7th	Red & Orange	12th	Black & Orange	17th	Yellow & Orange	22nd	Violet & Orange
3rd	White & Green	8th	Red & Green	13th	Black & Green	18th	Yellow & Green	23rd	Violet & Green
4th	White & Brown	9th	Red & Brown	14th	Black & Brown	19th	Yellow & Brown	24th	Violet & Brown
5th	White & Slate	10th	Red & Slate	15th	Black & Slate	20th	Yellow & Slate	25th	Violet & Slate

Color Code Chart No. 5 for Paired Cables (Western Electric Standard)

Pair No.	Color Combination	Pair No.	Color Combination	Pair No.	Color Combination	Pair No.	Color Combination	Pair No.	Color Combination
1	White / Blue Stripe	6	Red / Blue Stripe	11	Black / Blue Stripe	16	Yellow / Blue Stripe	21	Purple / Blue Stripe
2	Blue / White Stripe	7	Blue / Red Stripe	12	Blue / Black Stripe	17	Blue / Yellow Stripe	22	Blue / Purple Stripe
3	White / Orange Stripe	8	Red / Orange Stripe	13	Black / Orange Stripe	18	Yellow / Orange Stripe	23	Purple / Orange Stripe
4	Orange / White Stripe	9	Orange / Red Stripe	14	Orange / Black Stripe	19	Orange / Yellow Stripe	24	Purple / Green Stripe
5	White / Green Stripe	10	Red / Green Stripe	15	Green / Black Stripe	20	Yellow / Green Stripe	25	Green / Purple Stripe
	Green / White Stripe		Green / Red Stripe		Black / Brown Stripe		Green / Yellow Stripe		Purple / Brown Stripe
	White / Brown Stripe		Red / Brown Stripe		Brown / Black Stripe		Yellow / Brown Stripe		Brown / Purple Stripe
	Brown / White Stripe		Brown / Red Stripe		Black / Gray Stripe		Brown / Yellow Stripe		Purple / Gray Stripe
	White / Gray Stripe		Red / Gray Stripe		Gray / Black Stripe		Yellow / Gray Stripe		Gray / Purple Stripe
	Gray / White Stripe		Gray / Red Stripe				Gray / Yellow Stripe		