


low profile solids - for cable widths up to 2.00" (50,8 mm)

ULTRA-THIN. Excellent for thin flex circuits and SCSI 2 flat cables on .025" (0,64mm) centers. Six sizes accommodate cable widths up to 2.00" (50,8 mm).



PART No.	A	B	C	D	E	IMPEDANCE IN OHMS
28R0760	.760 19,3	.510 13,0	1.125 28,6	.300 7,6	.051 1,3	150 @ 100MHz
28R1127	1.125 28,6	.925 23,5	1.220 31,0	.303 7,7	.066 1,7	188 @ 100MHz
28R1127-2	1.125 28,6	.925 23,5	.980 24,9	.303 7,7	.066 1,7	151 @ 100MHz
28R1260	1.260 32,0	1.010 25,7	1.125 28,6	.300 7,6	.051 1,3	237 @ 100MHz
28R1575	1.575 40,0	1.325 33,7	1.125 28,6	.300 7,6	.051 1,3	160 @ 100MHz
28R1953	1.953 49,6	1.732 44,0	.472 12,0	.288 7,3	.059 1,5	109 @ 100MHz
28R2300	2.300 58,4	2.050 52,1	1.125 28,6	.300 7,6	.051 1,3	245 @ 100MHz

optional material formulations available upon request:

- microwave bluetooth™ 2.45 GHz peak

performance by part number:

