

300/200 Watts, 120v Industrial Soldering Gun



◀◀ previous print close next ▶▶

Product Details	
Catalog No.	D650
UPC Code	037103079480
Type	Single
Wattage	300 W / 200 W
Temperature Range	1100° F / 900° F
Cord Length	6 ft.
Components Supplied	7250
Packaging	Industrial Box / Carton
Tech. Spec.	Solder Safety Warnings.pdf
Low Res. Image	D650_100.jpg
High Res. Image	D650_300.jpg
Operating Ins.	D650_OI_PL.pdf
Parts List	D650_OI_PL.pdf
Stock Item	Normal Stock Item

Package Details (Dimensions)

Email this Page

Product Features:

- Reliable industrial quality tool
- Heavy-duty dual-heat gun produces 300 or 200 watts
- Highest power output of all our soldering guns
- 300 watts in high trigger (1st trigger position)
- 200 watts in low trigger (2nd trigger position)
- Nickel-plated copper secondary, heat-resistant thermoplastic housing
- Nickel-plated copper tip, and heavy-duty grounded cord
- Soldering, cutting and smoothing tips available
- UL and cUL listed