


1050N, 1052N and 1090N Series Non-Relampable Neon-Incandescent Indicator Lights

Description and Features



Mounting: Will snap-fit into Ø.500/.505 hole in panels .020/.100 thick. Push-on speednut SN0461 also available. Mounting hole pattern on page SP2.

Wire Leads: No. 22 AWG (105°C) 4.40/4.80 long, stripped .430/.570

Lens: Polycarbonate

Bezel: Polished stainless steel. For black finish add "X" after the series letter(s).

Housing: White Nylon

Lens Color	Neon	Incandescent	
	Model No. (105-125VAC)	Model No. (12V)	Model No. (28V)
Red	1050N1	1090N1-12V	1090N1-28V
Clear	1050N2	-	-
Amber	1050N3	1090N3-12V	1090N3-28V
White	1050N4	1090N4-12V	1090N4-28V
Green	1052N5*	1090N5-12V	1090N5-28V
Lamp used	C2A+Resistor	#2162	#2187
Lead Color	Black	Yellow	Purple

* Incorporates G2B lamp and resistor.

Underwriters Laboratories (UL) File No. E20325

Canadian Standards Association (CSA) File No. LR13346

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

VCC:

[1090N5-12V](#) [1090N1-28V](#) [1090N5-28V](#) [1090N1-12V](#) [1050N4](#) [1090N4-12V](#) [1090N4-28V](#) [1090NX1-12V](#) [1090NX1-28V](#) [1090NX3-12V](#) [1090NX3-28V](#) [1090NX4-12V](#) [1090NX4-28V](#) [1090NX5-12V](#) [1090NX5-28V](#) [1050N2](#) [1050NX1](#) [1050NX2](#) [1050NX3](#) [1050NX4](#) [1052NX5](#) [1090N3-6V](#) [1090N4-6V](#) [1090N5-6V](#) [1090N1-6V](#)