

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **39-00-0288**
Status: **Active**
Overview: Standard .093"
Description: 2.36mm Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1189, Female, with Tin (Sn) over Copper Plated Brass Contact, 14-20 AWG, Bag, with Dimple

Documents:

[Drawing \(PDF\)](#) [Product Specification PS-1189-008 \(PDF\)](#)
[Product Specification PS-1189-007 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Crimp Terminals
Series 1189
Application Power
Comments with Dimple
Crimp Quality Equipment Yes
Overview Standard .093"
Product Name Standard .093"
UPC 800753584402

Physical

Gender Female
Material - Metal Brass
Material - Plating Mating Tin
Material - Plating Termination Tin
Net Weight 339.000/mg
Packaging Type Bag
Plating min - Mating 0.889µm
Plating min - Termination 0.889µm
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 1.60-4.10mm
Wire Size AWG 14, 16, 18, 20
Wire Size mm² N/A

Material Info

Old Part Number 1189TL

Reference - Drawing Numbers

Product Specification PS-1189-007, PS-1189-008
Sales Drawing SD-1189-002




image - Reference only

EU RoHS

**ELV and RoHS
Compliant**
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

1189Series

Use With

3191 Receptacle

Application Tooling | FAQ

*Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.*

Global

Description	Product #
Extractor Tool for .093 and HCS-125 Product Series	<u>0638240200</u>
Hand Crimp Tool	<u>0638191100</u>