




NOTES:

- UL LISTED AND CSA CERTIFIED FOR:
 - 600V MAX VOLTAGE RATING
 - 257°F (125°C) MAX TEMP RATING (UL)
221°F (105°C) MAX TEMP RATING (CSA)
 - STRANDED COPPER WIRE ONLY
- 6-12 LBS INITIAL INSERTION/WITHDRAWAL FORCE
- PACKAGE QTY: -M=1000 PIECES, -C=100 PIECES
- MATERIAL:
 - STAMPING: TIN PLATED BRASS
 - HOUSING: TYPE 6/6 NYLON
- DIMENSIONS IN BRACKETS ARE IN mm OR mm²
- NYLON HOUSING IS TRANSLUCENT
- INSTALLATION TOOLS:
 - UL & CSA APPROVED: CT-520, CT-1525
(UTILIZE CT-1525 CRIMP POCKET "A")
 - PANDUIT APPROVED: CT-100
- WIRE STRIP LENGTH 9/32 ^{+1/32}₋₀ (7.1 ⁺⁸₋₀)

PART NUMBER		TAB SIZE	WIRE RANGE AWG (MM ²)	HOUSING COLOR (NOTE 6)	MAX. INSUL. DIA.	DIMENSIONS in.		
PREFIX	PK					A ^{±.03} (.8)	B ^{±.015} (.4)	C ^{±.015} (.4)
DNF18-110F1B	-C -M	.110 X .032 (2,8 X 0,8)	22-18 (0,38-1,0)	RED	.12 (3,0)	.71 (18,0)	.19 (4,8)	.16 (4,1)
DNF18-111F1B	-C -M	.110 X .020 (2,8 X 0,5)	22-18 (0,38-1,0)	RED	.12 (3,0)	.71 (18,0)	.19 (4,8)	.16 (4,1)



LISTED
20H3
E78522



CERTIFIED
LR31212

A41544_04

04	2/07	DAW	DAW	ADDED POCKET "A" NOTE TO CT-1525	TR00220	LCA	TRO	 PANDUIT CORP. TINLEY PARK, ILLINOIS			
03	7/03	KLFU	SKB	UPDATED DRAWING	12453	SKB	TRO				
02	5/98	TM	JW	ADDED CT-1525 TO TOOL NOTES	06872	LA	DBH				
01	10/94	TH	RLS	UPDATED NOTES AND DIMENSIONS	02550	LA	KS	LOOSE PIECE, NYLON, FULLY INSULATED FEMALE DISCONNECTS .110 X .032, .110 X .020 TAB SIZES			
REV	DATE	BY	CHK	DESCRIPTION	ECN#	CUST	PM		DRAWN BY BDK	CHK'D RLS	SCALE NONE