

Single-cut taps M ≈ DIN 352 HSS, ground

Chamfer: Type B,
4 - 5 threads with
progressive tap

Thread: metric, DIN ISO 13

Flanks: relief-ground

Tolerance: ISO 2 / 6H

Surface: bright

Right-hand cutting

For through threads in unalloyed or low-alloyed steels up to 800 N/mm² strength, malleable cast iron and non-ferrous metals. The thread can be cut in one operation by hand or machine.

Packing unit:
Individual plastic pack

Nominal thread size	Pitch mm	Thread core hole mm	Total length mm	Thread length mm	Article no.	Price each €
M 3	0,50	2,50	40,0	10,0	231 030	
M 4	0,70	3,30	45,0	12,0	231 040	
M 5	0,80	4,20	50,0	13,0	231 050	
M 6	1,00	5,00	50,0	15,0	231 060	
M 8	1,25	6,80	56,0	18,0	231 080	
M 10	1,50	8,50	70,0	24,0	231 100	
M 12	1,75	10,20	75,0	29,0	231 120	



1.6

Single-cut taps M ≈ DIN 352 HSS Co 5, ground

Chamfer: Type B,
4 - 5 threads with
progressive tap

Thread: metric, DIN ISO 13

Flanks: relief-ground

Tolerance: ISO 2 / 6H

Surface: bright

Right-hand cutting

For through threads in unalloyed or alloyed steels up to 900 N/mm² strength, malleable cast iron and non-ferrous metals. The thread can be cut in one operation by hand or machine. The machine tap consists of cobalt alloyed heavy-duty high-speed steel with higher heat-resistance for a longer tool life.

Packing unit:
Individual plastic pack

Nominal thread size	Pitch mm	Thread core hole mm	Total length mm	Thread length mm	Article no.	Price each €
M 3	0,50	2,50	40,0	10,0	231 030 E	
M 4	0,70	3,30	45,0	12,0	231 040 E	
M 5	0,80	4,20	50,0	13,0	231 050 E	
M 6	1,00	5,00	50,0	15,0	231 060 E	
M 8	1,25	6,80	56,0	18,0	231 080 E	
M 10	1,50	8,50	70,0	24,0	231 100 E	
M 12	1,75	10,20	75,0	29,0	231 120 E	

