

## **Type 1 Mild Steel Splitter Box** *CSB Series*

**Hinged Door with Screw**



### **Application**

- The splitter boxes are designed for indoor distribution of up to 600 V (max) service using either 3 or 4 wires.

### **Standards**

- CSA Type 1
- Complies with
  - IEC 60529, IP20

### **Construction**




- Formed and spot welded from 14 or 16 gauge steel.
- Factory installed splitter blocks.
- Series of knockouts on each side.
- Padlocking hasp.

### **Finish**

- Enclosure and cover are finished in ANSI 61 gray powder coating.

### **Accessories**

- Splitter Blocks
- Grounding Kits



NOTE: KNOCKOUTS TYPICAL ON OPPOSITE SIDES

| Part No. |         |         | CU/AL   | Dimensions |       |      |      |      |       | Ship Wt. | Conduit Size (Location) |      |        |
|----------|---------|---------|---------|------------|-------|------|------|------|-------|----------|-------------------------|------|--------|
| Less     |         |         | Amps    | A          | B     | C    | D    | E    | F     | lbs      | 1/2"                    | 3/4" | 2"     |
| 3 Wire   | 4 Wire  | Blocks  |         |            |       |      |      |      |       |          | 3/4"                    | 1"   | 1 1/2" |
| CSB73    | CSB74   | CSB70   | 70/70   | 12.00      | 10.00 | 4.00 | 2.75 | 2.25 | 9.00  | 9        | 1,3,7                   | 2,4  | -      |
| CSB103   | CSB104  | CSB100  | 125/120 | 15.00      | 10.00 | 4.00 | 2.75 | 2.25 | 12.00 | 10       | 1,2,7                   | 2,4  | -      |
| CSB203   | CSB204  | CSB200  | 225/225 | 18.00      | 12.00 | 5.00 | 3.00 | 3.50 | 15.00 | 16       | 1,3,7                   | 4    | 1,3    |
| CSB403   | CSB404  | CSB400  | 400/340 | 24.00      | 17.00 | 6.00 | 3.31 | 4.88 | 21.00 | 37       | -                       | -    | -      |
| CSB603*  | CSB604* | CSB600* | 600/574 | 30.00      | 24.00 | 7.00 | 4.00 | 5.00 | 27.00 | 63       | -                       | -    | -      |

\* 14 gauge steel

Data subject to change without notice