




- Short shank and compact heads.
- Ideal where access is restricted.
- Metric sizes from 3.2 to 17 mm.
- Inch sizes from 1/8" to 11/16".
- 12-point ring angled at 15°.
- H 6-point ring angled at 15°.
- Satin chrome finish.

Dessins Techniques



Zoom



		L mm	A mm	A "		B x B' mm	C x C' mm		 g
39.3,2H		77	3,2			10 x 7	3,1 x 3,1	CKS.61A	9
39.4H		77	4			10 x 8	3,1 x 3,1	CKS.61A	9
39.5H		82	5			11,8 x 9,	3,5 x 4	CKS.61A	10
39.5,5H		84	5,5			11,8 x 9,5	3,5 x 4	CKS.61A	10
39.6		90	6			15 x 10,4	4,1 x 5	CKS.61A	13
39.7		90	7			15 x 11,5	4,1 x 5	CKS.61A	13
39.8		94	8			17,2 x 12,5	4,5 x 5,8	CKS.61A	18
39.9		98	9			19,4 x 14	4,8 x 6	CKS.61A	25
39.10		103	10			21,5 x 15,3	5,1 x 6,4	CKS.61A	30
39.11		109	11			23,7 x 16,8	5,3 x 6,8	CKS.61A	35
39.12		127	12			26 x 18	5,5 x 7,5	CKS.61A	47
39.13		141	13			28 x 19,5	5,8 x 8	CKS.61A	54
39.14		147	14			30,2 x 20,8	6,0 x 8,5	CKS.61A	70
39.15		152	15			32,3 x 22,1	6,4 x 9	CKS.61A	80
39.16		158	16			34,4 x 23,6	6,7 x 9,6	CKS.61A	90
39.17		165	17			36,5 x 25	6,9 x 10	CKS.61A	100
39.1/8H		77		1/8"		10,0 x 7,0	3,1 x 3,1	CKS.61A	9
39.5/32H		77		5/32"		10,0 x 8,0	3,1 x 3,1	CKS.61A	9
39.3/16H		82		3/16"		11,8 x 9,0	3,5 x 4,0	CKS.61A	10
39.7/32H		84		7/32"		11,8 x 9,5	3,5 x 4,0	CKS.61A	10
39.1/4		90		1/4"		15,0 x 10,4	4,1 x 5,0	CKS.61A	13
39.9/32		90		9/32"		15,0 x 11,5	4,1 x 5,0	CKS.61A	13
39.5/16		94		5/16"		17,2 x 12,5	4,5 x 5,8	CKS.61A	18
39.11/32		98		11/32"		19,4 x 14,0	4,8 x 6,0	CKS.61A	25
39.3/8		103		3/8"		21,5 x 15,3	5,1 x 6,4	CKS.61A	30

Données Techniques

39.7/16	109	7/16"		23,7 x 16,8	5,3 x 6,8	CKS.61A	35
39.1/2	141	1/2"		28,0 x 19,5	5,8 x 8,0	CKS.61A	54
39.9/16	147	9/16"		30,2 x 20,8	6,0 x 8,5	CKS.61A	70
39.5/8	158	5/8"		34,4 x 23,6	6,7 x 9,6	CKS.61A	90
39.11/16	165	11/16"		36,5 x 25,0	6,9 x 10,0	CKS.61A	100