



T&B Conduit Fittings


EMT Fittings



Ideal for cramped locations or tight corners where large radius conduit elbows will not fit or would appear unworkmanlike. Shoulders on body of 1/2" size are hex-shaped to provide positive holding for standard installation tools. Use insulated type for simple, and safe, installations. Malleable iron. CSA rated 105°C.



Ideal for cramped locations or tight corners where large radius conduit elbows will not fit or would appear unworkmanlike. Shoulders on body of 1/2" size are hex-shaped to provide positive holding for standard installation tools.



For connecting EMT to threaded rigid and intermediate metal conduit.

Short Elbows—Insulated



Cat. No.	Size	Dimension (in.)		
		A	B	C
4240	1/2"	1-7/8	1-1/8	11/16
4241-TB	1/2"	1-11/16	1-3/8	1/2
4242	1"	1-7/8	1-5/8	5/8
4243-TB	1-1/4"	2-3/4	2-5/16	11/16
4244	1-1/2"	3-1/16	2-5/8	11/16
4245	2"	3-3/8	3-7/32	3/4

U.L. Listed and CSA Certified raintight.

Short Elbows Malleable Iron



Cat. No.	Size	Dimension (in.)		
		A	B	C
4230	1/2"	1-7/16	1-9/32	7/16
4231	3/4"	1-11/16	1-19/32	1/2
4232	1"	1-7/8	1-27/32	5/8
4233	1-1/4"	2-3/4	2-15/32	11/16
4234	1-1/2"	3-1/16	2-3/4	11/16
4235	2"	3-3/8	3-5/16	11/16

U.L. Listed and CSA Certified raintight.

Combination Coupling—Steel



Cat. No.	Size	Dimension (in.)	
		A	B
530-TB	1/2"	1-3/8	1-1/16
531	3/4"	1-1/2	1-11/32
532	1"	1-19/32	1-21/32

U.L. Listed and CSA Certified raintight.