




HARDWARE:



SWITCH FUNCTION

Model No.	POS. 1	POS. 2
DPW 1 CG	OFF	MOM
Term. Comm.	OPEN	SHORT

PANEL CUT-OUT



Compliance: RohS III (2015/863/EU)

Tolerances: 0.00: ±0.25mm 0.0: ±0.40mm			Date	Name	DPW 1 CG x
			08/07	dr	
Accessory	10/19	dr			
IP rating	07/11	dr			
Revised	11/10	dr			
Hardware	06/10	dr			30 12 18
Actuator color black	06/08	dr	knitter-switch		
Operating temperature	04/08	dr			
Water proofing	03/08	dr			
Modifications	Date	Name			
					Page
					1/2

Specifications:

Contact rating: max.: 400mA, 32V AC; 100mA, 50V DC; 125mA, 125V AC
Contact resistance: 50mOhm max.
Insulation resistance: 1GOhm min. at 500V DC
Dielectric strength: 1 000V AC
Operating temperature: -30°C to +85°C
Mechanical life: 1 000 000 cycles
Electrical life: 500 000 cycles
Operating force: 3N +/-1N
Soldering conditions: 350°C max., 3sec.
Travel: 1.5mm
Panel thickness: 1.5mm min.; 4.0mm max.
Torque: 0.5Nm max. applied to nut
Water proofing: IP 67
Material: Case: DAP UL94V-0
Bushing / cap: polyamide 6/6
Terminal / contact: gold over silver plated
IP rating: IP 67 (mounted)

X=CAP COLOR	
W	white
K	black
R	red
O	orange
Y	yellow
G	green
B	blue

Compliance: RohS III (2015/863/EU)

Tolerances: 0.00: ±0.25mm 0.0: ±0.40mm			Date	Name	DPW 1 CG x	
			08/07	dr		
Accessory	10/19	dr				
IP rating	07/11	dr				
Revised	11/10	dr				
Hardware	06/10	dr				
Actuator color black	06/08	dr	knitter-switch		30 12 18	Page
Operating temperature	04/08	dr				2/2
Water proofing	03/08	dr				
Modifications	Date	Name				