

A range of audio and video connectors incorporating many innovative features. Assembled and disassembly is screwless and is achieved by a few quick turns of the back shell.

-A single piece latch which is simple to operate, mating smoothly with both lockable and non-latching connectors.

-The strain relief collet ensures a positive cable grip.


-Pressed socket contacts which 'float' to assist 'wrap-round' contact with the pin, since they can 'move' with the pins should any movement occur between mating connectors.

-A range of coloured plastic coding rings, each with a single number moulded in, offering a quick and easy system of channel identification.

-Internal design feature allow for a quick and simple insert assembly.

**(Note: these connectors are not to be used for mains applications.)**

#### Dimensions



#### Electrical Properties

Number of contacts	3
Rated current per contact	16 Amps
Maximum wire size (solid)	10 AWG 6.0 mm <sup>2</sup>
Cap Between contacts	4 pF
Rated voltage	250 Volts ac
Test voltage	1500 Volts ac
Contact resistance	3m Ω
Insulation resistance	1G Ω

CONVERTED FROM PS857 ISS2 (13.09.96) IN JAN 2003

DrgNo 800-804-802-806

TITLE PROFESSIONAL QUALITY - CABLE SOCKET

ALL DIMENSIONS IN MM  
ANGLES IN DECIMAL DEGREES

GENERAL SPECIFICATION		CUSTOMER		FILTER REF	
Delttron Part No	Silver Contacts	Nickel	Black	Apvrd Date 03/02/03	Apvrd By MC Drwn by BS Scale: NTS Sheet 1 / 1

3-Way	
800-0300	804-0300 802-0300 806-0300

**DELTRON Components**

ISSUE

2

FOR

MULTIPOLE

CONNECTOR