Enjoy connections. Live

- *Multimedia*
- *Accesories*
- *Datacom*
- *Network*

Order online @

or call 1.800.344.4539

DIGITUS® External premium HDD enclosure 2.5" USB 2.0 & Firewire A

- External aluminium case for 2.5" hard drives
- Conforms to USB 2.0 or USB2.0 and IEEE1394a specification (DA-70502-1)
- Data transfer rate up to 480 Mbps (USB) and 400 bps (Firewire A)
- Two Firewire ports, 1x 6-pin and 1x 4-pin (DA-70502-1)
- Conforms to ATA/ATAPI-6 specification (Rev.1.0 for USB)
- Conforms to USB storage class specification Ver.1.0
- Compatible with Win98/SE, 2000, ME and XP
- Supports Mac OS 9.0, supports LINUX 2.4.x and better
- LED power (green)/ status (red)
- Power supply via USB port, external power supply (optional)

Make any drive an External Drive!
Keep your information protected on these high quality Enclosures!

Accessories

191896 / DA-70550 — DA-70550-ND
2,5" HDD enclosure USB 2.0

Click part number to purchase online @

DIGITUS® External S-ATA HDD enclosure 3.5" ALU

- Serial ATA 1.0 compliant
- Automation 3.0/1.5 Gbps transmission rate negotiation
- Support S-ATA Hot Plug
- Support S-ATA connector
- Thinner and longer cable
- Serialize/ Deserialize a 40 Bit (double word aligned) or 10 Bit with 4X speed signal from/to the link layer
- Provide specified OOB signal detection and transmission
- 32 Bits CRC error checking on all data and control information
- Supports 32 Bits and 48 Bits LBA hard disk
- Compatible with WIN98, WIN98 se, WIN 2000, WIN ME and WIN XP
- Support MAC OS which support S-ATA HDD

Accessories

192121 / DA-70585 — DA-70585-ND
DIGITUS External HDD enclosure 3.5" ALU S-ATA ⇨ S-ATA

Click part number to purchase online @

DIGITUS® USB 1.1 to PS/2 adapter

Accessories

117933 / DA-70118 — AE10287-ND
USB 1.1 ⇨ PS/2 adapter

Click part number to purchase online

DIGITUS® USB to serial adapter, USB 2.0

Accessories

170426 / DA-70146 — AE10289-ND
USB to serial adapter, USB 2.0

Click part number to purchase online

DIGITUS® USB to serial adapter, USB 1.1

Accessories

170426 / DA-70145 — AE10288-ND
USB to serial adapter, USB 1.1

Click part number to purchase online

USB to Serial Converter, DSUB 9 pin Male

Accessories

170426 / DA-70119 — AE1488-ND
USB to serial converter, 9pin, 25pin

Click part number to purchase online

USB Repeater Cable USB 2.0

Accessories

170426 / DA-70130 — AE10290-ND
USB repeater cable 2.0

Click part number to purchase online

DIGITUS® Pocket KVM switch PS/2, 2-port

- Controls two PCs with one PS/2 keyboard, one PS/2 mouse and one monitor
- Simple installation - no additional software required
- PC selection via hotkey
- Excellent video quality - up to 1920 x 1440 pixels 200 MHz bandwidth
- Supports DDC, DDC2, DDC2B, DDC2AB
- Hot Plug & Play
- Keyboard and mouse emulation for faultless booting of the computer
- Autoscan (5,10,15,20,25,30 sec. options) / autoskip function
- No external power supply required
- Integrated KVM cable for connection of two PCs 1.2 m
- Supports standard PS/2 mouse, Microsoft IntelliMouse and full support for Microsoft IntelliPoint 5.0 mouse driver and Logitech Mouse Ware driver
- Supports Windows 95/98/98SE/ME/NT4.0/2000/XP/VISTA, DOS, Linux, Novell Netware, FreeBSD

Datacom

159056 / DC-OC12
Pocket KVM switch PS/2, 2-port
DC-OC12-ND

Click part number to purchase online

DIGITUS® Pocket KVM switch PS/2, 2-port for USB PC

- Control two PCs with one PS/2 keyboard, one PS/2 mouse and one monitor
- Simple installation - no additional software required
- PC selection via hotkey
- Excellent video quality - up to 1920 x 1440 pixels, 200 MHz bandwidth
- Supports DDC, DDC2, DDC2B, DDC2AB
- Hot Plug & Play
- Keyboard and mouse emulation for faultless booting of the computer
- Autoscan (5,10,15,20,25,30 sec. options) / autoskip function
- No external power supply required
- Integrated KVM cable for connection of two PCs 1.5 m
- Supports standard PS/2 mouse, Microsoft IntelliMouse and full support for Microsoft IntelliPoint 5.0 mouse driver and Logitech Mouse Ware driver
- Supports Windows 95/98/98SE/ME/NT4.0/2000/XP, DOS, Linux, Novell Netware, FreeBSD
- Mouse and keyboard connection to USB-port of the PC

Datacom

159056 / DC-OC12U
Pocket KVM switch PS/2, 2-port
DC-OC12U-ND

Click part number to purchase online

DIGITUS® USB pocket KVM switch, 2-port

- Control two PCs with one USB keyboard, one USB mouse and one monitor
- Simple installation: No additional software required
- PC selection via hotkey
- Excellent video quality-up to 2048 x 1536 pixels at 85 HZ
- Support DDC, DDC2, DDC2B, DDC2AB
- Audio IN/OUT - support
- Hot Plug & Play
- Keyboard and mouse emulation for faultless booting of the computer
- Autoscan- (5 to 60 sec.)
- No external power supply required
- Integrated KVM cable for connection of two PCs 1.2 m
- Supports Windows 95/98/98SE/ME/NT4.0/2000/2003 Server/XP/VISTA, Linux, Mac and Sun Micro Systems

Datacom

206064 / DC-11402
USB pocket KVM switch, 2-port
DC-11402-ND

Click part number to purchase online

DIGITUS® USB-KVM switch, 2-port

- Controls two PCs with one PS/2 or USB-keyboard, one PS/2 or USB-mouse and one monitor
- Simple installation - no additional software needed
- PC-choice over push-buttons, Hot-Key or OSD-Utility
- Excellent video quality - up to 1920 x 1440 pixels
- Supports DDC, DDC2
- Hot Plug & Play
- Emulates a keyboard on each PC to allow your computers to boot normally without a keyboard error
- Autoscan- (5 bis 250 sec.)
- USB Bus Powered and downstream-port activated by external Power DC 5V 2A
- incl. 3-Port USB - Hub
- Supports Windows 95/98/98SE/ME/NT4.0/2000/2003 Server/XP/VISTA, Linux, Mac and Sun Micro Systems

Datacom

201076 / DC-11201-1
USB-KVM switch, 2-port
DC-11201-1-ND

Click part number to purchase online

DIGITUS® USB-PS/2-KVM switch

- Controls up to two PCs with one PS/2- or USB-keyboard, one PS/2- or USB-mouse and one monitor
- Simple installation - no additional software needed
- PC-choice over push-buttons or Hot-Key
- Excellent video quality - up to 2048 x 1536 pixels at 85 Hz
- Supports DDC, DDC2
- Hot Plug & Play
- Emulates a keyboard on each PC to allow your computers to boot normally without a keyboard error
- Autoscan (5 to 250 sec.)
- No external power supply needed, self powered through PS/2 and/or USB connection (optional Power supply 5V; 2,0A - Art.-Nr. DN-R-PS)
- Fully compliant with the USB 1.1/ 2.0 specification
- Supports Windows 95/98/98SE/ME/NT4.0/2000/2003 Server/XP/VISTA, Linux, Mac and Sun Micro Systems

Datacom

200994 / DC-11202-1
USB-PS/2-KVM switch, 2-port
DC-11202-1-ND

Click part number to purchase online

DIGITUS® USB-PS/2-KVM switch

- Controls up to four PCs with one PS/2- or USB-keyboard, one PS/2- or USB-mouse and one monitor
- Simple installation - no additional software needed
- PC-choice over push-buttons or Hot-Key
- Excellent video quality - up to 2048 x 1536 pixels at 85 Hz
- Supports DDC, DDC2
- Hot Plug & Play
- Emulates a keyboard on each PC to allow your computers to boot normally without a keyboard error
- Autoscan (5 to 250 sec.)
- No external power supply needed, self powered through PS/2 and/or USB connection (optional Power supply 5V; 2,0A - Art.-Nr. DN-R-PS)
- Fully compliant with the USB 1.1/ 2.0 specification
- Supports Windows 95/98/98SE/ME/NT4.0/2000/2003 Server/XP/VISTA, Linux, Mac and Sun Micro Systems

Datacom

201007 / DC-12202-1
USB-PS/2-KVM switch, 4-port
DC-12202-1-ND

Click part number to purchase online

DIGITUS® Wireless LAN USB 2.0 adapter, 802.11g

- IEEE 802.11b and IEEE 802.11g compatible
- Compliant to USB 2.0 standard
- Supported data transfer rates 54,11,5.5,2.0,1.0 Mbps
- 128-bit WEP (Wired equivalent privacy) encryption
- WPA and WPA2 encryption (Wireless fidelity protected access)
- Realtek-Chipset
- Suitable for all current network environments
- Support for Windows 98SE/ME/2000/XP

Easy Installation and great networking!

Network

200406 / DN-7003GT — DN-7003GT-ND
Wireless LAN USB 2.0 adapter, 802.11g

Click part number to purchase online @

DIGITUS® Wireless LAN PCI adapter, 802,11g

- IEEE 802.11b and IEEE 802.11g compatible
- 32 bit PC card compatible
- Supported data transfer rates 54,11,5.5,2.0,1.0 Mbps
- 128-bit WEP (Wired equivalent privacy) encryption
- Support for WPA and WPA2
- Realtek-Chipset
- Suitable for all current network environments
- Support for Windows 98SE/ME/2000/XP/Vista

Network

211655 / DN-7006GS — DN-7006GS-ND
Wireless LAN PCI adapter, 802,11g

Click part number to purchase online @

DIGITUS® Wi-Fi finder with integrated USB 2.0 wireless LAN adapter, 802.11g

- LC Display shows: Number of Access Points, Wi-Fi standard, Channel, SSID, encryption and Signal strength
- Shows several Access Points in the Wireless LAN environment
- Blue lightend, easy to read LC Display
- Integrated rechargeable long life battery, charged over the USB Port
- Easy to use, Simple function keys on the device
- Integrated USB Wireless LAN Adapter based on Zydas chipset
- IEEE 802.11b and IEEE 802.11g compatible
- Supported data transfer rate 54,11,5.5,2.0,1.0 Mbps
- Security: 64/128/256-bit WEP Data Encryption, WPA/WPA2 (TKIP with IEEE 802.1x) and AES
- Suitable for all current network environments
- Support for Windows XP,2000

Detect WiFi signals with out a computer!

Network

195535 / DN-7020 — DN-7020-ND
Wi-Fi Finder with integrated USB 2.0 wireless LAN adapter

Click part number to purchase online @

DIGITUS® Fast Ethernet N-Way 8 Port Desktop Switch

- IEEE 802.3 and IEEE 802.3u compatible
- 20/200 MBit full duplex
- Automatic speed and half/full duplex detection / configuration
- Store and forward architecture
- Auto MDI / MDI-X function
- CE compliant
- External power supply

Network

136750 / DN-5002C — DN-5002C-ND
N-Way Desktop Switch, 8-port

Click part number to purchase online

DIGITUS® is a Trademark of ASSMANN Electronics

DIGITUS®

DIGITUS® Microscope camera with built-in light

Amazing 200x magnification and Live View at 30fps!

The universal digital microscope camera shows objects in „live view" with up to 200x magnification on the computer screen. The built-in bright LED lighting guarantees for sharp and brilliant pictures.

- Universal microscope camera for the computer with built-in white and bright lighting
- Magnification continuous 10 - 200x
- Screen capture resolution 640 x 480 pixel
- "Live view" with up to 30 fps
- USB 1.1 / 2.0 interface
- 1,8m USB Cable length
- Ideal for business and hobby e.g.

for industrial inspection like textile and printing,
for skin and scalp examination,
for stamp, coin and gem collectors,
for science and learning.
As reading aid.

- Incl. desktop stand, manual and capture software on CD-ROM
- For Windows-PC operating WIN98SE, ME, 2000, XP, Vista and Mac

Multimedia

200154 / DA-70350 — DA-70350-ND
Digital USB Microscope

Click part number to purchase online @

Perfect gift for everyone, even youself!
Bright image and outstanding quality, built in 4 in 1 Card Reader!

DIGITUS® Digital photo frame

- 7" Screen size
- Memory card slot for SD and MMC memory cards
- Slideshow for JPEG files
- Slideshow interval adjustable
- Autoplay when inserting memory card
- Keys for the simple controlling of important functions (Play/Pause, Prev, Next, Interval, Modus)
- Vertically, horizontal arrangeable and additionally with hanging for wall fastening

Technical features

- Size: 7 inch
- Resolution: 480 x 234
- Brightness: 350 cd/m2
- Contrast: 300
- View angle: 60/60/5 (CR>10)
- Response time: 30 ms
- Format: JEPG

Multimedia

211358 / DA-70871 — DA-70871-ND
Digital photo frame

Click part number to purchase online @

Top of the line USB HUBS & Card Readers!

DIGITUS® „Twister" notebook USB 2.0 Hub

- 4 x USB A female, each twistable about 180 degree
- 1 x USB A male, integrated and twistable about 180 degree
- Space-saving design, direct Pluggable to the notebook without additional cable
- High-quality „softtouch" material
- With status LED and connector for an additional power supply
- USB 2.0 and USB 1.1 compatible
- Supports Hot Plug and Plug & Play

Accessories

205890 / DA-70213-1 — DA-70213-1-ND
„Twister" notebook USB 2.0 Hub

Click part number to purchase online @

DIGITUS® USB 2.0 Hub, 4-and 7-Port

- USB 2.0 and USB 1.1 compatible
- 4 und 7 x USB A, female (USB 1.1 and 2.0 devices)
- Maximum data transfer rate 480 Mbps (USB 2.0)
- Over current protection on all outputs
- Hot Plug and Plug & Play compatible
- Additional USB cable and power supply included
- Plastic housing with aluminiumdesign
- Operating system support for Windows XP / Vista and MAC OS 10.x and higher

Accessories

211884 / DA-70224 USB 2.0 Hub, 4-port	DA-70224-ND
211891 / DA-70227 USB 2.0 Hub, 7-port	DA-70227-ND

Click part number to purchase online @

DIGITUS® USB 2.0 mini Hub

- USB 2.0 and USB 1.1 compatible
- 4 x USB A, female (USB 1.1 and 2.0 devices)
- Maximum data transfer rate 480 Mbps (USB 2.0)
- Over current protection on all outputs
- Hot Plug and Plug & Play compatible
- Power supply via USB
- Additional USB cable included
- Operating system support for Windows XP / Vista and MAC OS 10.x and higher

Accessories

157229 / DA-70132-1 USB 2.0 mini Hub, 4-port	DA-70132-1-ND

Click part number to purchase online @

DIGITUS® USB 2.0 card reader 56in1

- Compliant to USB 2.0 specification
- Supports USB High Speed 480 Mbps and Full Speed 12 Mbps
- Supports Media Copy and Hot -Swap
- Supports Hot Plug, Plug & Play
- Supports following memory cards: Compact Flach (CF) series, Memory Stick (MS) series, Smart Media (SM) + XD series, Secure Digital (SD), T-Flash series
- Bus powered
- USB connection cable incl.
- Supported OS: WIN 98SE/ ME/ 2000/ XP / Vista, Mac OS 10.x

Accessories

211907 / DA-70316-1 Card reader USB 2.0 56in1	DA-70316-1-ND

Click part number to purchase online @

DIGITUS® USB 2.0 multi card reader

- Supports MS, MS Pro, MS Duo, MS Pro Duo, HS MS, SD, mini SD, MMC, RS-MMC, Trans-Flash
- Compliant with USB 2.0
- Complies with USB Storage Class specification Rev. 1.0
- Operating System Supported: Windows 98SE/ME/2000/XP/Vista, Mac 9.x/X, Linux

Accessories

205746 / DA-70310 USB 2.0 multi card reader	DA-70310-ND

Click part number to purchase online @

USB HUB + Card Reader all in one unit!

DIGITUS® USB 2.0 card reader 56in1 + Hub

- Compliant to USB 2.0 specification
- Supports USB High Speed 480 Mbps and Full Speed 12 Mbps
- Supports Media Copy und Hot -Swap
- Supports Hot Plug, Plug & Play
- Supports following memory cards: Compact Flach (CF) series, Memory Stick (MS) series, Smart Media (SM) + XD series, Secure Digital (SD) series
- Integrated 3-port Hub
- USB connection cable and power supply incl.
- Supported OS: WIN 98SE/ ME/ 2000/ XP / Vista, Mac OS 10.x

Accessories

184669 / DA-70312 Card reader USB 2.0 56in1 + Hub	DA-70312-ND

Click part number to purchase online @

DIGITUS® USB webcam

- Manual adjustable fokus, automatic whitebalance, automatic exposure
- Resolution: 480k Pixel, 800x600, 640x480, 352x288, 320x240, 176x144, 160x120
- Framerates: up to 30 fps
- Color: 24 Bit TrueColor
- Color depth: 32 Byte
- JPEG-compression integrated
- Operatin System: Win 2000/ XP / Vista

Excellent laptop Add-on!

Multimedia

211631 / DA-70812 DA-70812-ND
USB webcam

Click part number to purchase online @

DIGITUS® USB webcam

- Built-in microphone
- Manual adjustable fokus, automatic whitebalance, automatic exposure
- Resolution: 480k Pixel, 800x600, 640x480, 352x288, 320x240, 176x144, 160x120
- Framerates: up to 30 fps
- Color: 24 Bit TrueColor
- Color depth: 32 Byte
- JPEG-compression integrated
- incl. driver and VP EYE software
- Operatin System: Win 2000/ XP / Vista

Built-in Microphone,
Start your webconference right away!

Multimedia

211648 / DA-70814 DA-70814-ND
USB webcam

Click part number to purchase online @

DIGITUS® USB Bluetooth 2.0 EDR adapter

- Bluetooth 1.1 / 1.2 / 2.0 and USB 1.1 compatible
- Supported data rates: up to 3 Mbps(Max)
- Range: up to 80 m DN-3017, up to 150m DN-3018
- CSR Bluetooth Chipset
- Toshiba Bluetooth Software
- Suitable for Windows 98 SE / ME / 2000 / XP
- Dimension: (LxWxH) 59 x 7 x 19 mm
- Weight: 8 g

Bluetooth2.0 high speed

Turn your PC into a Bluettoth device
the next edge on communications!

Multimedia

193708 / DN-3018 DN-3018-ND
USB Bluetooth 2.0 EDR adapter, class 1

Click part number to purchase online @

DIGITUS® Bluetooth audio transmitter

- Bluetooth Audio Transmitter: Plug into your Stereo audio source via audio jack in your MP3 .PSP, PC, TV, DVD player, ipod, home audio system …etc.
- Compatible with Bluetooth 1.1 / 1.2 standard
- Data transfer rate up to 732 kbps
- Range up to approx. 15m
- Ultra-compact design
- Rechargeable polymer battery
- Working time up to 6,5 hours
- Automatically pair with Stereo Bluetooth headphone by pressing a button
- Support A2DP profile
- Size: 52 x 14 x 22 mm

Bluetooth™

Multimedia

195702 / DN-3014 DN-3014-ND
Bluetooth audio transmitter

DIGITUS® USB 2.0 IDE & SATA cable

- Support 1,8"/2,5"/3,5" IDE and Serial ATA HardDisk
- Support SATA, SATA II
- Compliance with USB 2.0 (Hi-Speed)
- Compliance with USB Mass Storage Class
- Support 480 Mbps High Speed (HS) and 12 Mbps Full Speed USB operation
- Support ATA/ATAPI Ultra DMA Mode
- Support ATA/ATAPI PACKET command feature set
- Support ATA/ATAPI LBA48 Bit addressing mode
- Support dual LUN (Logic Unit Number) with automatically master/slave enumeration
- High-Speed Data Transfer, Low Power Consumption
- Red / green LED's indicating operation
- Operating System Support: Windows 98SE/ME/2000/XP/2003/Vista

Accessories

195580 / DA-70148-1 — DA-70148-1-ND
USB 2.0 IDE & SATA cable

Click part number to purchase online @

DIGITUS® USB 2.0 to IDE adapter cable

- USB 2.0 compliant
- Support for ATA / ATAPI devices
- Cable length 1,2 m
- inclusive 2,5" Adapter
- Support for: Windows XP, Windows 2000

Accessories

171003 / DA-70147 — DA-70147-ND
USB 2.0 to IDE adapter cable

Click part number to purchase online @

DIGITUS® 2.5" Hard drive installation kit including 2.5" to 3.5"

To install 2.5" hard drives in 3.5" drive slots

Supplied:
- Two metal installation brackets including screws
- Adapter for 40 pin IDE cable and power supply adapter

Accessories

170372/DA-70430 — DA-70430-ND
2.3" HDD Installation Kit

Click part number to purchase online @

DIGITUS® Notebook cooler pad with Hub and CardReader

- Metallcase
- 2 powerfull, silent Fan
- 3 Port USB 2.0 Hub integrated (DA-70341)
- 4 Slot Multicardreader with USB 2.0 Interface is integrated (DA-70341)
- Support for: CompactFlash, Micro Drive, Memory Stick, Memory Stick pro, Secure Digital, MultiMedia Card
- Support für Windows 98/2000/XP

Accessories

205753 / DA-70341 — DA-70341-ND
Notebook cooler pad, with Hub and CardReader

Click part number to purchase online @

DIGITUS® USB Fingerprint sensor USB stick version

- Fingerprint-Sensor for efficient, high security and convenience access to the notebook computer
- Never need anymore passwords, only the users thumb
- User-friendly integration of fingerprint authentication for login, internet access and applications
- The delivered software manage logins, users passwords and data encryption for files, folders and virtual drives and inserts the user data automatically in required data fields after successful fingerprint scan
- Semiconductor sensor, swipe type
- 192 x 16 pixel, 8 bit / pixel, 508 dpi resolution
- ESD +/- 15 kV
- False rejection rate < 1:1.000
- False acceptance rate < 1:1.000.000
- Matching time < 1 second
- USB 1.1 interface / bus powered
- Power LED
- Supports Windows 98 / ME / 2000 / XP / Vista

Protect your information, use your fingerprint instead of password!

Accessories

206019 / DA-70700 — DA-70700-ND
USB fingerprint-sensor - USB stick version

Click part number to purchase online @

DIGITUS® is a Trademark of ASSMANN Electronics