


1. QUALITY CONFORMANCE INSPECTION PER MIL-C-55302 (GROUP A, B & C).
2. PACKAGED PER MIL-C-55302
3. THESE DIMENSIONS PERTAIN TO CAVITY CENTERLINES ONLY, NOT TO CONTACT LOCATIONS.
4. SLOT OPTIONAL AT INDICATED AREA OF HOUSING.
5. CONTACTS: 0.00127[.000050] GOLD OVER 0.000762 TO 0.00381 [.000030 TO .000150] NICKEL ENTIRE CONTACT.
6. MARKED IN APPROXIMATE AREA SHOWN
EXAMPLE: AMP PART NO
 DATE CODE MILITARY PART NUMBER
HOUSINGS SMALLER THAN 20 POSITION ARE MARKED AS FOLLOWS:
10 THRU 18 POSN - AMP TRADEMARK AND PART NUMBER
8, 6 AND 4 POSN - AMP TRADEMARK ONLY (MAY BE ROTATED 90° TO FIT).
7. CHARACTERS MARKED IN AREA SHOWN, EVERY FIFTH POSITION MARKED WITH A BAR
8. "CSA" LOGO MARKED ON HOUSING.
9. OBSOLETE



RECOMMENDED PC BOARD HOLE LAYOUT

						LOC	DIST	P		F		ZONE		LTR		H		REVISONS															
																		DESCRIPTION										DATE		APPD			
						REV										PER										0630-0408-00		CT		1-01		DN	
M55302/128-DR1D						166.12 [6.540]	64	130	9	6-87965-4	M55302/128-BR1D						84.84 [3.340]	32	66	3-87965-2													
M55302/128-DQ1D						163.58 [6.440]	63	128	9	6-87965-3	M55302/128-BQ1D						82.30 [3.240]	31	64	3-87965-1													
M55302/128-DP1D						161.04 [6.340]	62	126	9	6-87965-2	M55302/128-BP1D						79.76 [3.140]	30	62	3-87965-0													
M55302/128-DN1D						158.50 [6.240]	61	124	9	6-87965-1	M55302/128-BN1D						77.22 [3.040]	29	60	2-87965-9													
M55302/128-DM1D						155.96 [6.140]	60	122	9	6-87965-0	M55302/128-BM1D						74.68 [2.940]	28	58	2-87965-8													
M55302/128-DL1D						153.42 [6.040]	59	120		5-87965-9	M55302/128-BL1D						72.14 [2.840]	27	56	2-87965-7													
M55302/128-DK1D						150.88 [5.940]	58	118		5-87965-8	M55302/128-BK1D						69.60 [2.740]	26	54	2-87965-6													
M55302/128-DJ1D						148.34 [5.840]	57	116		5-87965-7	M55302/128-BJ1D						67.06 [2.640]	25	52	2-87965-5													
M55302/128-DH1D						145.80 [5.740]	56	114		5-87965-6	M55302/128-BH1D						64.52 [2.540]	24	50	2-87965-4													
M55302/128-DG1D						143.26 [5.640]	55	112		5-87965-5	M55302/128-BG1D						61.98 [2.440]	23	48	2-87965-3													
M55302/128-DF1D						140.72 [5.540]	54	110		5-87965-4	M55302/128-BF1D						59.44 [2.340]	22	46	2-87965-2													
M55302/128-DE1D						138.18 [5.440]	53	108		5-87965-3	M55302/128-BE1D						56.90 [2.240]	21	44	2-87965-1													
M55302/128-DD1D						135.64 [5.340]	52	106		5-87965-2	M55302/128-BD1D						54.36 [2.140]	20	42	2-87965-0													
M55302/128-DC1D						133.10 [5.240]	51	104		5-87965-1	M55302/128-BC1D						51.82 [2.040]	19	40	1-87965-9													
M55302/128-DB1D						130.56 [5.140]	50	102		5-87965-0	M55302/128-BB1D						49.28 [1.940]	18	38	1-87965-8													
M55302/128-DA1D						128.02 [5.040]	49	100		4-87965-9	M55302/128-BA1D						46.74 [1.840]	17	36	1-87965-7													
M55302/128-CR1D						125.48 [4.940]	48	98		4-87965-8	M55302/128-AR1D						40.20 [1.740]	16	34	1-87965-6													
M55302/128-CQ1D						122.94 [4.840]	47	96		4-87965-7	M55302/128-AQ1D						41.66 [1.640]	15	32	1-87965-5													
M55302/128-CP1D						120.40 [4.740]	46	94		4-87965-6	M55302/128-AP1D						39.12 [1.540]	14	30	1-87965-4													
M55302/128-CN1D						117.86 [4.640]	45	92		4-87965-5	M55302/128-AN1D						36.58 [1.440]	13	28	1-87965-3													
M55302/128-CM1D						115.32 [4.540]	44	90		4-87965-4	M55302/128-AM1D						34.04 [1.340]	12	26	1-87965-2													
M55302/128-CL1D						112.78 [4.440]	43	88		4-87965-3	M55302/128-AL1D						31.50 [1.240]	11	24	1-87965-1													
M55302/128-CK1D						110.24 [4.340]	42	86		4-87965-2	M55302/128-AK1D						28.96 [1.140]	10	22	1-87965-0													
M55302/128-CJ1D						107.70 [4.240]	41	84		4-87965-1	M55302/128-AJ1D						26.42 [1.040]	9	20	87965-9													
M55302/128-CH1D						105.16 [4.140]	40	82		4-87965-0	M55302/128-AH1D						23.88 [.940]	8	18	87965-8													
M55302/128-CG1D						102.62 [4.040]	39	80		3-87965-9	M55302/128-AG1D						21.34 [.840]	7	16	87965-7													
M55302/128-CF1D						100.08 [3.940]	38	78		3-87965-8	M55302/128-AF1D						18.80 [.740]	6	14	87965-6													
M55302/128-CE1D						97.54 [3.840]	37	76		3-87965-7	M55302/128-AE1D						16.26 [.640]	5	12	87965-5													
M55302/128-CD1D						95.00 [3.740]	36	74		3-87965-6	M55302/128-AD1D						13.72 [.540]	4	10	87965-4													
M55302/128-CC1D						92.46 [3.640]	35	72		3-87965-5	M55302/128-AC1D						11.18 [.440]	3	8	87965-3													
M55302/128-CB1D						89.92 [3.540]	34	70		3-87965-4	M55302/128-AB1D						8.64 [.340]	2	6	87965-2													
M55302/128-CA1D						87.38 [3.440]	33	68		3-87965-3	M55302/128-AA1D						6.10 [.240]	1	4	87965-1													
MILITARY PART NUMBER						B	A	NO OF POSN		PART NUMBER	MILITARY PART NUMBER						B	A	NO OF POSN		PART NUMBER												