


SEALS

ISO-K Clamp Flange Components

CENTERING RING		DN ... ISO-K	Part No.	A	B	C	D
Inner & outer ring: Seal:	Aluminum 6082/– Elastomer CR	63	212-251	96	70	3.9	8
		80	212-091	109	83	3.9	8
		100	212-252	128	102	3.9	8
		160	212-253	179	153	3.9	8
		200	212-254	239	213	3.9	8
		250	212-255	287	261	3.9	8
		320	212-256	358	318	5.6	14
		400	212-257	440	400	5.6	14
		500	212-258	541	501	5.6	14
		630	212-259	691	651	5.6	14
Inner & outer ring: Seal:	Aluminum 6082/– Elastomer FPM	63	212-261	96	70	3.9	8
		80	212-092	109	83	3.9	8
		100	212-262	128	102	3.9	8
		160	212-263	179	153	3.9	8
		200	212-264	239	213	3.9	8
		250	212-265	287	261	3.9	8
		320	212-266	358	318	5.6	14
		400	212-267	440	400	5.6	14
		500	212-268	541	501	5.6	14
		630	212-269	691	651	5.6	14
Inner ring: Outer ring: Seal:	Stainless steel 304/– Aluminum 6082/– Elastomer FPM	800	212-270	840	800	5.6	14
		1000	212-271	1040	1000	5.6	14
		63	212-281	96	70	3.9	8
		80	212-093	109	83	3.9	8
		100	212-282	128	102	3.9	8
		160	212-283	179	153	3.9	8
		200	212-284	239	213	3.9	8
		250	212-285	287	261	3.9	8




CENTERING RING WITH FINE FILTER

Inner ring: Stainless steel 304/–
Outer ring: Aluminum 6082/–
Seal: Elastomer FPM
Snap ring: Stainless steel 304/–
Filter grit: Stainless steel 304/–

Filter: Stainless steel 316L/–
Pore size 0.004 mm
Degree of separation at
0.001 mm up to 98%

DN ... ISO-K	Part No.	A	B	C	D
63	212-291	62	69.8	3.9	8
100	212-292	94	101.8	3.9	8




O-RING

	DN ... ISO-K	Part No.	A	B	Set of
Elastomer CR	63	212-386	75.6	5.3	5 pcs.
	80	212-387	88.3	5.3	5 pcs.
	100	212-388	107.3	5.3	5 pcs.
	160	212-389	158.1	5.3	5 pcs.
	200	212-390	208.9	5.3	5 pcs.
	250	212-391	253.4	5.3	5 pcs.
	320	212-356	329.6	7	
	400	212-357	405.3	7	
	500	212-358	506.9	7	
Elastomer FPM	630	212-359	658.9	7	
	63	212-392	75.6	5.3	5 pcs.
	80	212-393	88.3	5.3	5 pcs.
	100	212-394	107.3	5.3	5 pcs.
	160	212-395	158.1	5.3	5 pcs.
	200	212-396	208.9	5.3	5 pcs.
Elastomer FPM	250	212-397	253.4	5.3	5 pcs.
	320	212-366	329.6	7	
	400	212-367	405.3	7	
	500	212-368	506.9	7	
	630	212-369	658.9	7	
	800	212-370	808	7	
	1000	212-371	1006	7	



ALUMINUM SEAL

	DN ... ISO-K	Part No.	A	B	C	D	E
Aluminum annealed 6082/-	63	212-301	85.6	83	69.8	2.6	4.5
	100	212-302	116.6	114	101.8	2.6	4.5
	160	212-303	166.6	164	152.8	2.6	4.5
	250	212-305	276.6	274	260.8	2.6	4.5
Number of		Clamps	Claw Grips				
	DN 63 ISO -K	4					
	DN 100 ISO-K	6	8				
	DN 160 ISO-K	8	8				
	DN 250 ISO-K	12	12				



GLOBAL HEADQUARTERS:

Two Technology Place, East Syracuse, NY 13057 USA
Tel: +1.315.434.1100 Fax: +1.315.437.3803 E-mail: reachus@inficon.com

UNITED STATES FRANCE GERMANY LIECHTENSTEIN SWITZERLAND UNITED KINGDOM CHINA JAPAN KOREA SINGAPORE TAIWAN

Visit our website for contact information and other sales offices worldwide. www.inficon.com
Due to our continuing program of product improvements, specifications are subject to change without notice.
qiba09e1 (2004-05) ©2003 INFICON Inc.