

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [58721-0010](#)
Status: **Active**
Overview: Heavy Duty Rectangular Connectors - HMC™
Description: HMC™ Rectangular Industrial Hood Bracket, Multi-Module Type, 48-72 Circuits, Type A Polarization

Documents:

3D Model	Product Specification PS-58719-006 (PDF)
Drawing (PDF)	Application Specification AS-58723-004 (PDF)
Product Specification PS-58719-005 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

TUV R72081037

General

Product Family	I/O Connectors
Series	58721
Application	Panel-Mount
Component Type	Hood Bracket
Overview	<u>Heavy Duty Rectangular Connectors - HMC™</u>
Product Name	HMC™
Type	N/A

Physical

Circuits (Loaded)	48
Circuits (maximum)	48
Lock to Mating Part	Yes
Material - Plating Mating	n/a
Orientation	Vertical
Packaging Type	Bag
Panel Mount	N/A
Pitch - Mating Interface	N/A
Polarized to Mating Part	Yes
Temperature Range - Operating	-55°C to +125°C
Termination Interface: Style	N/A
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP65

Electrical

Current - Maximum per Contact	12A, 20A
Voltage - Maximum	250V AC

Material Info

Reference - Drawing Numbers

Application Specification	AS-58723-004
Product Specification	PS-58719-005, PS-58719-006, RPS-58719-003, RPS-58719-004, RPS-58719-006, RPS-58719-007, RPS-58719-008
Sales Drawing	SD-58721-002




image - Reference only

Series

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[58721Series](#)

Mates With

[587190010](#) panel mount bracket

Use With

[51194](#) housing, [51195](#) housing, [587230010](#)
hood, [51203](#) housing, [51204](#) housing