

# LAMINATED TRANSFORMERS

Type UI30 / 16.5 - 10VA



## AGENCY APPROVALS

1. UL 506, File E113449   
3. EN61558




**Pulse**  
A TECHNITROL COMPANY

| Primary (V) | Secondary (V / mA) | No-Load Voltage (V) | Part Number       | Agency Approvals |
|-------------|--------------------|---------------------|-------------------|------------------|
| 2x115       | 6/833 / 6/833      | 9.00/9.00           | <b>030-7073.0</b> | 1/3*             |
| 2x115       | 9/555 / 9/555      | 13.40/13.40         | <b>030-7076.0</b> | 1/3*             |
| 2x115       | 12/416 / 12/416    | 17.20/17.20         | <b>030-7079.0</b> | 1/3*             |
| 2x115       | 15/333 / 15/333    | 21.70/21.70         | <b>030-7082.0</b> | 1/3*             |
| 2x115       | 18/277 / 18/277    | 24.80/24.80         | <b>030-7085.0</b> | 1/3*             |
| 2x115       | 21/238 / 21/238    | 29.50/29.50         | <b>030-7088.0</b> | 1                |

\*NOTE: When checking the approval status of this product with VDE, add the prefix "BV" and the suffix "L" to the orderable Part Number (these letters will also be found on the part label). The prefix and suffix are not part of the orderable Part Number.

- Frequency 50/60Hz
- Potted under vacuum
- Split-bobbin
- Temperature class  $t_a$  40°C/B
- Weight: 0.24kg
- Packaging unit: 15 pieces (tray)
- Fixing material for  $\square$  2,5mm (0.098 inch)
  - Self-tapping screws: DIN 7513 (M 3x8)
  - Sheet-metal screws: DIN 7971 (2,9x6,5)

## Mechanical



## Schematics

