

平面ハンドル

FLUSH HANDLES

A-1750
ステンレス製

特徴 Feature

PAT.PEND.

- 扉を閉めるだけのワンタッチロック
- 新機構で止め金かじりの問題点を改良
- ステンレス製で耐食性に優れています。
- 右開き用・左開き用(本図・写真共右開き用です。)

- One-touch locking only by closing the door.
- New mechanism is incorporated in the stopper plate for improvement.
- Corrosion-resistant stainless steel is used.
- The left-hand or right-hand use. (Drawings and photo show the right-hand use.)

仕様 材質: 冷間圧延ステンレス鋼板(SUS304)
表面仕上: ヘアライン仕上

- 鍵番号: 0200
- 付属品: ビスセット・キー2本付属
- 適用板厚: 0~3.2mm
- 配分電盤・制御盤

用途
納期
備考

- ラッチのカバーを外してからラッチを取り付けてください。(A-1750-2~4)
- 永くご使用頂くために定期的に摺動部に高性能潤滑剤C-985(1367ページ)を塗布してください。
- 本製品の錠前はキー先端部での操作となります。
- 鍵を必要以上に回転させると錠前部・鍵先端部が破損する恐れがありますのでご注意ください。

Specifications • Material: Cold rolled stainless steel (SUS304)
• Finish: Hairline finish





- Key No.: 0200
- Accessories: Screws and two keys
- Applicable panel thickness: 0~3.2mm

Specific use • Power/distribution and control boards
Remarks • Remove the latch cover before fitting the latch on the handle.

- To prolong the life of the product, apply a regular coating of high-performance lubricant C-985 (P.1367) to the sliding parts.
- The lock on this product is operated with the tip of the key.
- Note that care is required, since turning the key more than is necessary risks damaging the lock or the tip of the key.

キーNo.0200
Key

A-1750-1-1R

パネル穴明け寸法
Panel drilling dimensions使用例
Example of application

※品番が変更になりました。A-1750-B-1~4→A-1750-1~4 Product No. has been changed.

商品番号 Product No.	RoHS CAD	備考 Remarks	L ₁	L ₂	L ₃	L ₄	L ₅	L ₆	L ₇	W ₁	W ₂	W ₃	W ₄	W ₅	W ₆	W ₇	(H ₁)	H ₂	H ₃	H ₄	H ₅	(S)	P	製品質量(g) Mass	コード Code	単価 Price	量販価格 数量 Quantity	単価 Price	
A-1750-1-1L	●	左開き用 Left-hand use	142	55	30.5	16	80	76	120	33	15	25	14	61	24	27	68	3.5	31.5	18	10	16	7.5	128	240	03583	¥3,850	5個～	¥3,696
A-1750-1-1R	● 2D/3D	右開き用 Right-hand use																								03582	¥3,850	5個～	¥3,696
A-1750-2-1L	●	左開き用 Left-hand use	117	48	25	13	63	59.5	98	29	12	20	16	50	22	24	45.5	3	26.5	15	8	13.5	6.0	105	160	03585	¥3,300	5個～	¥3,168
A-1750-2-1R	● 2D	右開き用 Right-hand use																								03584	¥3,300	5個～	¥3,168
A-1750-3-1L	●	左開き用 Left-hand use	84	48	25	13	30	26.5	65	29	12	20	16	50	22	24	25	3	26.5	15	8	13.5	6.0	72	140	03587	¥3,200	5個～	¥3,080
A-1750-3-1R	● 2D	右開き用 Right-hand use																								03586	¥3,200	5個～	¥3,080
A-1750-4-2L	●	左開き用 Left-hand use	70	42	20	9	22	18.5	51	25	10	20	15	40	18	22	24.5	3	23.5	14	6.5	12.5	4.5	58	90	01579	¥2,400	5個～	¥2,304
A-1750-4-2R	● 2D	右開き用 Right-hand use																								02687	¥2,400	5個～	¥2,304

●: RoHS指令対応品 ▲: RoHS指令に対応可能です。

※大量のご注文は更にお安くなります。